

Pressure sensor

96760



Connector 		Dimensions 	
Media	Liquid media e.g. fuel, engine oil air and exhaust	Pressure range	E.g. 0 ... 6 bar, relative *
Temperature range	- 40 °C to + 125 °C	Output signal	0.5 ... 4.5 V ratiometric
Thread	M18 x 1.5 *	Connector	DIN Bajonett (DIN 72585), Female connector on request
Protection range	IP 6K9K		

* Other types and values on request