



4500
LUMEN



3 1/2 - 15H
RUNTIME



74M
RANGE



IP65/IK07
IP RATING

NEW SP-4500 - RECHARGEABLE BLUETOOTH SPEAKER WORK LIGHT

- 4500 lumen 45W white COB LED, 6500K
- High quality integrated 10W Bluetooth speaker
- Dual power - rechargeable & mains powered
- Power bank function for charging devices
- Ultra tough nylon-polymer construction
- Concealed 360° rotating aluminium hanging hook
- 140° vertical adjustable body to angle light
- IP65 dust & water resistant
- IK07 shock proof - 2m drop resistant
- 5 Battery level and charging indicator lights
- Multi-country mains charger included
- 3 1/2 hours charge time
- Optional extra magnet and tripods available

BATTERY 11.1v 5200mAh Li-ion
Rechargeable Battery

WEIGHT 1560g

DIMENSION 210 x 210 x 100mm



CONCEALED ALUMINIUM
HANGING HOOK



BATTERY LEVEL AND
CHARGING INDICATOR LIGHTS

