

**NEW!**



## Nonconductive Lockout Hasps

- Made of strong, rigid red plastic resin
- Offers high flexibility, resistance to cracking and most chemicals
- Has excellent electrical insulating characteristics
- Performs at low temperatures, excellent heat resistance
- Lockout Shackle fits in holes with a diameter of minimum 10 mm
- Max. shackle diameter: 9 mm
- Min. shackle clearance: 20 mm
- Packaging: 1 piece

Part No.	Description
045582	Nonconductive Lockout Hasp



## Nylon Lockout Hasp

- Nonconductive nylon hasps accommodates up to 6 locks
- Withstands up to 450 kg, yet weighs only 30 g
- Locks out any piece of equipment safely and effectively
- Lockout Shackle fits in holes with a diameter of minimum 7 mm
- Max. shackle diameter: 9 mm
- Min. shackle clearance: 20 mm
- Packaging: 1 piece

Part No.	Description
236916	Nylon Lockout Hasp

## Brass I.D. Tags

- Instant identification of assigned padlock user
- Withstands rugged work environments
- Can be engraved by using engraver or stamp kits
- Max. shackle diameter: 9.5 mm

Part No.	Description	Packaging
265378	Brass tags & attachment rings	12
265379	Collars and rivets	12



## Padlock Eyes

Some equipment needs modification to accept locks and Lockout devices. These padlock eyes can help you to do this. Available in two versions:

- Surface mounted eyes made of hard wrought steel (angle of 90°)
- Tamper resistant inside mounting eyes (flat)
- 38 mm wide
- Max. shackle diameter: 13 mm

Part No.	Description	Packaging
065686	Surface mount	6 pairs
065687	Inside mount	1 pair



## Safety Lockout

- Allow six workers to lock out a single energy source
- Vinyl coated high tensile steel
- Available in red and yellow
- Available in 2 sizes
- Max. shackle diameter: 9.5 mm
- Min. shackle clearance: 20 mm
- Packaging: 12 pieces

Part No.	Shackle width	Colour
265375	25 mm	Red
265376	38 mm	Red
225209	25 mm	Yellow
225210	38 mm	Yellow



## Lockout Starter Kit

- 2 x 25 mm Safety Lockouts (one red and one yellow)
- 2 x 38 mm Safety Lockouts (one red and one yellow)
- 6 x 38 mm Brady Safety Padlocks (one of each colour)
- 1 x Nylon Lockout hasp

Part No.: 805856

