



Creating Safe Work Solutions During COVID-19

T30R-1515-KUQ

▶ PRODUCTS FOR INDUSTRIAL AUTOMATION



T30R R-GAGE Series Radar Sensor
Range 15 m; Input 10-30 V dc
0-10 V Analog, 1 NPN/PNP Configurable with IO Link
5 Pin Euro (M12) Quick Disconnect
Part Number: 808901



ACCESSORIES TO COMPLETE YOUR SYSTEM

Add all or individual items to your cart. More options available below.





SMB30A

Bracket: Right Angle Mounting
Material: 12 Gauge Stainless Steel
Curved mounting slot for versatility/orientation
Clearance for M6 (1/4 in.) hardware

In Stock



Contact Us

	<p>PRO-KIT</p> <p>DK-Pro Series Accessory Kit Includes Converter Cable, Splitter and Power Supply</p> <p>In Stock</p>
	<p>MQDEC2-506</p> <p>Euro-Style Quick Disconnect Cable with Shield 5-Pin Straight Connector 2 m (6.5 ft) in Length Chrome-plated brass coupling nut</p> <p>In Stock</p>

SPECIFICATIONS

Sensing Beam	Radar
PC Configurable	Yes
Operating Frequency	122 GHz
Sensing Mode (General)	Proximity
Sensing Mode (Detailed)	Time of Flight
Housing Style	Barrel
Device Type	Sensor
Primary Housing Material	PBT
Input/Output	Analog & Discrete
Indicator	LED(s)
Analog Output Configuration	0-10 V dc
Connection	Integral QD
Radar Beam Pattern (H x V °)	15 x 15
Quick Disconnect Type	M12 (Euro)
Analog Resolution/Discrete Repeatability	< 1 mm at Excess Gain $\geq 10x$ < 10 mm at Excess Gain < 10x
Max Sensing Distance (mm)	15000



Contact Us

Minimum Sensing Distance (mm)	150
Sensing Beam	Radar
Power Supply	12-30 V dc
Delay at Power-up (ms)	300
Adjustments	Software; Push Button; Remote Teach
Number of Pins	5
Vibration	MIL-STD-202F req. Method 201A (vibration:10 to 60Hz max., double amplitude 0.06", max acc. 10G).
Mechanical Shock	MIL-STD-202G, Meth. 213B, conditions H&I (Shock: 75G with unit operation: 100G for non-operation).
Output Saturation Voltage NPN Outputs	< 3 V at 50 mA
Output Saturation Voltage PNP Outputs	< 3 V at 50 mA
Analog Voltage Output Rating	2.5 k Ω min. load impedance
Max Discrete (Switched) Output (mA)	50
Discrete (Switched) Outputs	1 NPN/PNP Configurable
Output Protection	Protected against short circuit
IP Rating	IP67
Max Operating Temperature (°C)	65
Min Operating Temperature (°C)	-40
Max Op. Relative Humidity Non-Condensing (%)	95 at 50°C
Minimum Response Time (ms)	6
Analog Linearity (mm)	+/- 4 mm from 300 to 600 mm; +/- 15 mm from 600 mm to 15 m
Barrel Diameter (mm)	30
Minimum Window Size (mm)	20
Remote Teach and Laser Control Input Impedence	55 k Ω
Discrete Output Hysteresis (mm)	Manually settable from 50 to 15000 mm


[Contact Us](#)


Max Off-state Leakage Current (μA)	NPN: < 40 at 30 V dc; PNP: < 10 at 30 V dc
Power/Current Consumption (exclusive of load)	100 mA max @ 24 V dc
Supply Protection Circuitry	Protected against reverse polarity and transient overvoltages
Feature: Remote Teach	Yes
Feature: Clear Object Detection	Yes
Feature: Timing (Hold/Delay)	Yes
Feature: Chemical Resistant	No
Common Ethernet Protocol	No
IO Link	Yes
PROFINET	No
RS-232	No
RS-422	No
RS-485	No
SSI	No
Wireless	No
1-wire Serial Interface	No
Profibus	No
Cert: US	Yes
Cert: European	Yes

COMPATIBLE PRODUCTS

BRACKET



Contact Us

	<p>SMB1815SF</p> <p>Bracket: Swivel with set screws for mounting Black reinforced thermoplastic polyester Used for mounting of T18 or T30 by its cable hub Hardware included</p>
	<p>SMB30A</p> <p>Bracket: Right Angle Mounting Material: 12 Gauge Stainless Steel Curved mounting slot for versatility/orientation Clearance for M6 (1/4 in.) hardware</p>
	<p>SMB30C</p> <p>Bracket: Stainless Steel Mounting Material: Black VALOX 30mm split clamp Hardware included</p>
	<p>SMB30FA</p> <p>SMB30FA Bracket: Swivel with Tilt and Pan Movement 30mm Mounting Hole 3/8-16x2in Bolt Thread Mount</p>
	<p>SMB30FAM10</p> <p>SMB30FAM10 Bracket: Swivel with Tilt and Pan Movement 30mm Mounting Hole M10-1.5x50 Bolt Thread</p>
	<p>SMB30FVK</p> <p>SMB30FVK Bracket: V-Clamp Flat with Fasteners for Mounting Sensor with 30mm Threads to Pipe or Extrusions 32.6mm (1.28in)</p>
	<p>SMB30MM</p> <p>Bracket: 30mm Material: 12 Gauge Stainless Steel Curved mounting slot for versatility/orientation Clearance for M6 (1/4 in.) hardware</p>
	<p>SMB30RAVK</p> <p>Bracket: V-Clamp Mount 30 mm hole to 28 mm tube Right-angle</p>
	<p>SMB30S</p> <p>Bracket: Plastic Material: Black Polyester 30 mm Swivel Hardware included</p>

[Contact Us](#)

	<p>SMB30SC</p> <p>Bracket: Compact 30 mm Swivel Black reinforced thermoplastic polyester Wide Range of Articulation Hardware included</p>
	<p>SMB30SM</p> <p>Bracket: Swivel Material: Black VALOX Swivel ball is locked when bolts are tightened Hardware included</p>
	<p>SMBAMS30P</p> <p>Bracket: 30 mm flat bracket Material: 12 Gauge Cold Rolled Steel Curved mounting slot for versatility/orientation</p>
	<p>SMBAMS30RA</p> <p>Bracket: 30mm Right Angle Material: 12 Gauge cold rolled steel Curved mounting slot for versatility/orientation</p>

PRO CONVERTER CABLE

	<p>PRO-KIT</p> <p>DK-Pro Series Accessory Kit Includes Converter Cable, Splitter and Power Supply</p>
---	--

DOUBLE-ENDED CORDSETS

	<p>MQDEC3-506SS</p> <p>Euro-style Quick Disconnect Cable Double-ended 5-pin Male Connector Straight 5-pin Female Connector Straight 1.83 m Length Chrome Plated Brass Coupling Nut; Shield Wire Grounded to Coupling Nut</p>
	<p>MQDEC3-515SS</p> <p>Euro-style Quick Disconnect Cable Double-ended 5-pin Male Connector Straight 5-pin Female Connector Straight 4.58 m Length Chrome plated brass coupling nut; Shield wire grounded to coupling nut</p>



Contact Us

MQDEC3-530SS

Euro-style Quick Disconnect Cable
 Double-ended 5-pin Male Connector Straight
 5-pin Female Connector Straight 9.2 m Length
 Chrome plated brass coupling nut; Shield wire grounded to coupling nut

SINGLE-ENDED CORDSETS**MQDEC2-506**

Euro-Style Quick Disconnect Cable with Shield
 5-Pin Straight Connector
 2 m (6.5 ft) in Length
 Chrome-plated brass coupling nut

MQDEC2-506RA

Euro-Style Quick Disconnect Cable with Shield
 5-Pin Right-Angle Connector
 2 m (6.5 ft) in Length
 Chrome-plated brass coupling nut

MQDEC2-515

Euro-Style Quick Disconnect Cable with Shield
 5-Pin Straight Connector
 5 m (15 ft) in Length
 Chrome-plated brass coupling nut

MQDEC2-515RA

Euro-Style Quick Disconnect Cable with Shield
 5-Pin Right-Angle Connector
 5 m (15 ft) in Length
 Chrome-plated brass coupling nut


MQDEC2-530

Euro-Style Quick Disconnect Cable with Shield
 5-Pin Straight Connector.C
 9 m (30 ft) in Length
 Chrome-plated brass coupling nut

MQDEC2-530RA

Euro-Style Quick Disconnect Cable with Shield
 5-Pin Right-Angle Connector
 9 m (30 ft) in Length
 Chrome-plated brass coupling nut


[Contact Us](#)

	<p>MQDEC2-550</p> <p>Euro-Style Quick Disconnect Cable with Shield 5-Pin Straight Connector 15 m (50 ft) in Length Chrome-plated brass coupling nut</p>
	<p>MQDEC2-550RA</p> <p>Euro-Style Quick Disconnect Cable with Shield 5-Pin Right-Angle Connector 15 m (50 ft) in Length Chrome-plated brass coupling nut</p>

SPLITTERS

	<p>CSB-M1251M1251B</p> <p>Euro-style Quick Disconnect Splitter Cable 5-Pin Straight male Eurofast 0.30 m (1 ft) Trunk 5-Pin Straight Female Eurofast 0.30m (1 ft) Branch 1 5-Pin Straight Female Eurofast 0.30 m (1 ft) Branch 2 Nickel Plated Brass Coupling Nuts Black Jacket</p>
--	--



Banner Engineering Corp. | 9714 Tenth Avenue North | Minneapolis, MN 55441 | United States of America



Contact Us