

## MB Self Adhesive Cable Tie Mounts

### Features and Benefits

Available in either 'screw mount or 'self adhesive mounting' this range offers a safe and secure mount.


Simple to install with a screw or bolt they give excellent security, particularly in areas of high vibration.

The Self Adhesive mounts are designed to offer the maximum surface area, and in conjunction with the specially developed adhesive ensures that a very high pull-off force is achieved.


The MB mounts offer '4-way' entry for the cable tie enabling quicker and more flexible installation.

### Application

Designed specifically for holding heavier cable bundles these mounting bases can be used in many industries from agriculture to truck manufacture. They offer a very secure fixing and can be used with a wide variety of heavy duty cable ties up to 8mm wide.



Cable Tie Mounts MB and TY




Cable Tie Mounts MB3A

**For more information on the types of adhesive used please turn to page 96.**


Material Data	
Material	<b>Polyamide 6.6 (PA66)</b>
Operating Temperature	<b>-40 °C to +85 °C Continuous, (+105 °C for 500 h)</b>
Flammability	<b>UL94 V2 (excluding adhesive)</b>




(halogenfree)



Cable Tie Mounts MB2A



Cable Tie Mounts MB3-5(A)



Cable Tie Mounts MB4CA

Technical Table

Article-No.	Type	Length (L)	Width (W)	Height (H)	Fixing Hole Ø (FH)	Fixing Hole Centres (F)	Strap Width max. (G)	Material	Colour	Adhesive
151-00135	MB2A	13.0	13.0	4.1	–	–	2.7	PA66	Black (BK)	Synthetic rubber
151-01802	MB2A	13.0	13.0	4.1	–	–	2.7	PA66	Natural (NA)	Synthetic rubber
151-01806	MB2AM	13.0	13.0	4.1	–	–	2.7	PA66	Black (BK)	–
151-01808	MB2AM	13.0	13.0	4.1	–	–	2.7	PA66	Natural (NA)	–
151-28320	MB3A	19.0	19.0	3.8	3.1	13.2	4.1	PA66	Black (BK)	Synthetic rubber
151-28707	MB3A	19.0	19.0	3.8	3.1	13.2	4.1	PA66	White (WH)	Synthetic rubber
151-00115	MB3AM	19.0	19.0	4.3	3.1	13.2	3.5	PA66	Black (BK)	–
151-28725	MB3AM	19.0	19.0	4.3	3.1	13.2	3.5	PA66	Natural (NA)	–
151-28412	MB4A	28.0	28.0	4.7	4.0	20.2	5.4	PA66	Black (BK)	Synthetic rubber
151-28417	MB4A	28.0	28.0	4.7	4.0	20.2	5.4	PA66	White (WH)	Synthetic rubber
151-28423	MB4AM	28.0	28.0	4.7	4.0	20.2	5.6	PA66	Black (BK)	–
151-28425	MB4AM	28.0	28.0	4.7	4.0	20.2	5.6	PA66	Natural (NA)	–
151-28529	MB5A	38.0	38.0	6.4	4.7	25.3	10.0	PA66	Natural (NA)	Synthetic rubber
151-28602	MB5A	37.7	37.7	7.4	4.7	25.3	10.0	PA66	Black (BK)	Synthetic rubber

All Dimensions in mm. Subject to technical changes.



Please Note for Product Specific Approvals please refer to Chapter 7.3