



**19" Digital LED TV
with built-in satellite tuner**

- 19" HD Ready widescreen TV
- Screen resolution: 1366 x 768px
- Built-in Freeview HD and Digital Freeview Channels
- Built-in satellite tuner
- HDMI input for your external devices and consoles
- Can be wall mounted (100mm x 100mm)

	EAN	5060750400968
Specifications	Model No.	C1920S
	Chipset	MSD3663LSA
	Sales Market	UK
	VESA Size	100 x 100
	Wall Mount Screws	M4 x 8
	Speaker Output	2 x 3W
	Actual Size of Display(Diagonal)	18.5"

Display	Display Type	LED
	Resolution	1366 x 768
	Brightness (nit)	200
	Contrast	1000:1
	Display Colours	16.7M
	Refresh Rate	60Hz
	Viewing Angle H/V	45/45/33/33
	Reponse Time	5ms

Accessories	Remote	1
	Battery	AAA x 2

Terminals		
	HDMI Input	1
	RCA Component + AUDIO Input	1
	RCA Composite + AUDIO Input	1
	15-PIN VGA + AUDIO Input	1
	RF Input	2
	USB Input	1
	Optical Digital AUDIO output	1
	3.5mm Headphone Output	1

Features		
	DVB-S	Yes
	DVB-S2	Yes
	DVB-T	Yes
	DVB-T2	Yes
	CI	Yes
	3D Digital Comb Filter + 3D Noise Reduction	Yes
	Automatic Volume Control	Yes
	Sleep Timer	Yes
	NO Signal Shut Down	Yes
	Adjustable Bass & Treble Controls	Yes
	Adjustable Balance Control	Yes
	Picture Modes	Standard/dynamic/soft/user
	Preset Sound Modes	Standard/music/movie/user
	OSD Menu Language	English/French/Spanish/Italy/Germany/Portugal
	Aspect Ratio Modes	wide/zoom/cinema/normal
	PVR	Yes

Power		
	Power Supply	AC 100V-240V - 50Hz/60Hz
	Operation Power Consumption	17W
	Max Power Consumption	36W
	KWh/annum	25kWh
	Standby Consumption	<0.5W
	Energy Efficiency Class	A

Dimensions		
	Unit Dimensions w Stand (mm)	440 x 160 x 307
	Unit Dimensions w/o Stand (mm)	440 x 44 x 275
	Weight (kg)	2.35