



## PRODUCT SET-UP SHEET

<b>LAUNCH DATE</b>	08/12/2020
<b>BRAND</b>	OPTOMA
<b>DESCRIPTION</b>	Document Camera / Visualiser
<b>SUPPLIER EAN NUMBER</b>	5055387664418
<b>PART NUMBER</b>	DC552
<b>MSRP</b>	TBA
<b>MODEL NO.</b>	DC552

### General

ATTRIBUTE	FACT
RESOLUTION	XGA, UXGA, 720p, 1080p (UXGA recording not supported)
PIXELS	13M PIXELS
FRAME RATE	UP TO 30fps
ZOOM OPTICAL	17 X
ZOOM DIGITAL	8 X
FOCUS	AUTO / MANUAL
IMAGE CAPTURE	DIRECT TO SD CARD OR USB "Flash Drive", USB/B TO PC
IMAGE ROTATION	SOFTWARE ROTATION (-180° ~ 0° ~ 180°)
ROTATING LENS	-90°/0°/90° MECHANICAL ROTATE
IMAGE MIRROR	YES
IMAGE FREEZE	YES
IMAGE PIP	YES
BRIGHTNESS ADJUSTMENT	YES
WHITE BALANCE	AUTO/MANUAL
NOISE	SILENT
POWER CONSUMPTION	5V DC POWER ADAPTOR
VOLTAGE	100-240V, 50-60Hz
VISA MOUNTING HOLES	YES 75mm

### Outputs

15 PIN VGA	YES
15 PIN VGA PASS THROUGH	YES
HDMI	YES
HDMI PASS THROUGH	YES
RS232	YES
SD CARD (MAX 32GB)	YES
USB/B to PC	YES
USB Fash Drive Support "Max 512GB"	YES
SPEAKER	YES
MICROPHONE	YES

### Dimensions(operating)

Width	80
Depth	520
Height	423
Weight	2.39

### Features

## Description

The New DC552 features a 13-megapixel sensor, 17x Optical zoom, 8x Optical Zoom and 4x Mechanical Zoom second video (at full resolution) for stunning image quality and performance allowing you to see detail often not possible with the camera function and include them in future presentation – it's all so easy. The new Fold Neck design allows you to easily capture images, video and audio with the DC552 Document Camera. Create more engaging lesson content by easily capturing images, video and audio with the DC552 Document Camera. experiment with the document camera, save it on your PC/Laptop via USB Flash Drive or save to a SD Card and use them during presentations for later review.

## ACCESSORIES INCLUDED

REMOTE CONTROL (with 2 AAA batteries)

AC ADAPTER with EU and UK Plugs

SETUP DISK INCLUDING SOFTWARE FOR WINDOWS 7/8/10, MAC OSX AND USER MANUAL IN ENGLISH

VGA CABLE

HDMI CABLE

USB 2.0 CABLE (Type A to B)

MICROSCOPE ADAPTORS (fit Ø28mm, Ø31mm, Ø33mm and Ø34mm)

ANTI-GLARE SHEET

## Key Features

- 13MP Camera
- XGA, UXGA, 720P, 1080P support (UXGA recording not supported)
- X17 Optical Zoom
- VGA Out
- VGA - In (Pass-through)
- HDMI Out
- HDMI - In (Pass-through)
- A3 Supported
- Fold Neck Design for easy storage
- USB Flash Drive (Max 512Gb) and SD CARD Slot (32GB max)
- RS232
- Audio In 3.5mm Jack
- Audio Out 3.5mm Jack
- Built-in microphone
- 3x mode brightness LED Lamp
- Smart DC software (Windows 7/8/10 and MAC OSX)



## Additional Information

### Carton Dimensions

Length

32

Width	47.5
Height	14
Weight	3.9
QTY PER OUTER	
OUTERS PER LAYER	
NUMBER OF LAYERS	
TOTAL UNITS per PALLET	
COMMODITY CODE	8525803000
EAN	5055387664418



**UNIT OF MEASUREMENT**


TO PROJECTOR OR PANEL
TO PROJECTOR OR PANEL
TO PROJECTOR OR PANEL
TO PROJECTOR OR PANEL
CONTROL
SAVE IMAGES OR VIDEO
LIVE VIDEO
SAVE IMAGES OR VIDEO
3.5mm Jack
3.5mm Jack

mm
mm
mm
kg

om for a 544x total zoom and upto 30 frames-per-  
ot visible to the human eye. Take photos or video using  
vs for easy storage under lock and key.

Camera. You can even take a video of a science  
and use it in your next class and students can record

SH, FRENCH, DEUTSCH AND SPANISH



cm	
cm	
kg	
4	
4	
4	
64	