


Laborkarte



RE315-LF



- Epoxyd FR4 1,5 mm, einseitig 35 µm CU
- heißverzinkt (HAL-leadfree)
- Lochraster 2,54 x 2,54 mm
- Lochdurchmesser 1,0 mm
- Größe 100 x 160 mm
- Steckverbinder 32/ 64/ 96-polig DIN 41612 Bauform C