



Data sheet | Item number: 762-4205/8000-001

Touch Panel 600; 39.6 cm (15,6"); 1920 x 1080 pixels; 2 x ETHERNET, 2 x USB, Audio; Visu Panel



www.wago.com/762-4205/8000-001



RoHS
Compliant



Item description

PIO2 hardware configuration

- 2 x ETHERNET port for connecting to field devices and the engineering tool
- 2 x USB port for optional connection of a USB stick, mouse or keyboard
- Audio interface for connecting a headphone or loudspeaker

Data

Technical data

Display diagonal	39.6 cm (15.6 Inches)
Display	Resistive touchscreen
Display colors	16.7 million colors
Graphics resolution	(1920 x 1080) px
Visualization	Webserver Web Visu
ETHERNET protocols	DHCP DNS FTP FTPS

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG
Hansastr. 27
32423 Minden
Phone: +49571 887-0 | Fax: +49571 887-169
Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
We are always happy to take your call at 01788 568 008.



	HTTP HTTPS SSH
Communication	EtherNet/IP™ Adapter (Slave), library for e!RUNTIME (prerequisite: e!RUNTIME PLC 600 license) Modbus TCP Master/Slave (prerequisite: e!RUNTIME PLC 600 license) EtherCAT Master, requires an additional license and an existing e!RUNTIME PLC 600 license on the device
Operating system	Real-time Linux (with RT-Preempt patch)
Processor	ARM® Cortex™ A9
Programming environment	e!COCKPIT (based on CODESYS V3)
Main memory (RAM)	2,048 MB
Internal memory (flash)	4096 MB
Program memory	32 MB
Data memory	128 MB
Memory card type	microSD (max. 2 GB); microSDHC (max. 32 GB)
Indicators	five LEDs
Controls	Two brightness settings (High and Low) on the front
Supply voltage	SELV DC 24 V (18 ... 31.2 V); with reverse voltage protection

Connection data

Connection technology: communication/fieldbus	Modbus TCP: 2 x RJ-45; 2 x USB 2.0 host (type A)
---	--

Physical data

Width	420 mm / 16.535 inch
Height	283 mm / 11.142 inch
Depth	58 mm / 2.283 inch
Panel cutout (W x H)	(406 x 268) mm

Mechanical data

Weight	2870 g
--------	--------

Environmental requirements

Surrounding air temperature (operation)	-20 ... 45 °C (in vertical mounting position; -20 ... +40 °C, other mounting positions)
Surrounding air temperature (storage)	-20 ... 70 °C
Protection type	IP65

Subject to changes. Please also observe the further product documentation!


Note on protection type	IP65 (front side); IP20 (rear side), per EN 60529
Relative humidity (without condensation)	90 %
Mounting type	Clamping elements (included) or VESA mount (4 x M4x8)

Commercial data

Packaging type	BOX
Country of origin	DE
GTIN	4055144002690
Customs tariff number	8471410000

Compatible products

software



Item no.: 2759-208/211-1000
Library MTP; Single License; Online activation

www.wago.com/2759-208/211-1000



Item no.: 2759-216/211-1000
e!RUNTIME; IEC 61131 runtime environment; 600; Single License; Online activation

www.wago.com/2759-216/211-1000



Item no.: 2759-2286/211-1000
e!RUNTIME; BACnet; 600; M; Single License; Online activation

www.wago.com/2759-2286/211-1000



Item no.: 2759-266/211-1000
e!RUNTIME; EtherCAT Master; 600; Single License; Online activation

www.wago.com/2759-266/211-1000



Item no.: 2759-286/211-1000
e!RUNTIME; BACnet; 600; Single License; Online activation

www.wago.com/2759-286/211-1000

assembling



Item no.: 762-9001
e!DISPLAY7300T ; Clamping elements (4 pieces)

www.wago.com/762-9001

memory card



Item no.: 758-879/000-3102
Memory Card SD Micro; 2 GByte

www.wago.com/758-879/000-3102



Item no.: 758-879/000-3108
Memory Card SD Micro; pSLC-NAND; 8 GB; Temperature range: -40 to 90°C

www.wago.com/758-879/000-3108

Subject to changes. Please also observe the further product documentation!



Downloads Documentation

Manual

WAGO Touch Panel 600 Standard Line	1.5.0 01-Dec-2020	pdf 2.5 MB	Download
---------------------------------------	----------------------	---------------	----------

Bid Text

762-4205/8000-001		xml 7.0 kB	Download
-------------------	--	---------------	----------

762-4205/8000-001		docx 20.3 kB	Download
-------------------	--	-----------------	----------

System Description

Touch Panel 600, system description		pdf 727.2 kB	Download
-------------------------------------	--	-----------------	----------

Installation Notes

Product family

Standard Line
[Show all products from the family](#)

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG
Hansastr. 27
32423 Minden
Phone: +49571 887-0 | Fax: +49571 887-169
Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
We are always happy to take your call at 01788 568 008.