

EcoTank ET-2714



DATASHEET / BROCHURE



This 3-in-1 inkjet is great for busy households looking to reduce their printing costs and enjoy mobile printing.

Reduce your cost of ink by 90% on average with Epson's cartridge-free ET-2714 EcoTank¹, which is supplied with high yield ink bottles. Its enhanced ultra-high ink filling system is easy and mess-free to fill thanks to the specially engineered ink bottles. Busy households are sure to appreciate this convenient solution that lets you forget about ink costs and running out of ink.

Minimise refills with cartridge-free printing

While keeping on top of ink replacements is unlikely to be on anyone's priority list, running out of ink can be a massive hassle. EcoTank provides a stress-free solution - from the first set of inks its ultra-high capacity ink tanks can hold the equivalent of 88 cartridges' worth of ink¹ on average. It's great for those that print lots as it minimises changing supplies.

Slash ink costs

This economical printer can save 90% on ink costs on average¹. With one set of ink you can produce an impressive 4,500 pages in black and 7,500 in colour².

Specially engineered for ease of use

EcoTank is more compact and easier to use than ever before. Its front-facing tanks are engineered for mess-free refills and the bottles are designed to only allow the correct colours to be inserted. Thanks to the front ink level display, it's easy to see when it's finally due for a refill.

Print from almost anywhere

It's easy to print from mobiles, tablets and laptops using EcoTank. With Wi-Fi and Wi-Fi Direct, you can send documents to print from smart devices using the Epson iPrint³ app. It can even receive files from almost anywhere in the world via Epson Email Print³.

Peace of mind

With a Micro Piezo printhead, EcoTank provides a reliable printing solution which is backed by a one year warranty.

KEY FEATURES

- **Save 90% on the cost of ink¹**
Equivalent of 88 cartridges' worth of ink included¹
- **Ultra-low-cost printing**
Print up to 4,500 pages in black and 7,500 pages in colour²
- **Next generation ink filling system**
Enjoy hassle and mess-free refills with the enhanced ink bottles
- **Wi-Fi & apps**
Print from mobile devices³
- **3-in-1 with front loading tank**
Print, copy & scan

PRODUCT SPECIFICATIONS

TECHNOLOGY

Printing Method	Epson Micro Piezo™ print head
Minimum Droplet Size	3 pl
Ink Technology	Dye Ink
Printing Resolution	5,760 x 1,440 DPI
Nozzle Configuration	180 Nozzles Black, 59 Nozzles per Color
Category	Home
All-in-One Functions	Print, Scan, Copy

PRINT

Printing Speed ISO/IEC 24734	10 pages/min Monochrome, 5 pages/min Colour, 69 Seconds per 10 x 15 cm photo
Maximum Printing Speed	33 pages/min Monochrome (plain paper 75 g/m ²), 15 pages/min Colour (plain paper 75 g/m ²), 27 Seconds per 10 x 15 cm photo (Epson Premium Glossy Photo Paper)
Colours	Black, Cyan, Yellow, Magenta

For detailed information on printing speeds please visit <http://www.epson.eu/testing>.

SCAN

Optical Resolution	1,200 DPI x 2,400 DPI (Horizontal x Vertical)
Scanner type	Contact image sensor (CIS)

PAPER / MEDIA HANDLING

Number of paper trays	1
Paper Formats	A4 (21.0x29.7 cm), A5 (14.8x21.0 cm), A6 (10.5x14.8 cm), B5 (17.6x25.7 cm), B6 (12.5x17.6 cm), C6 (Envelope), DL (Envelope), No. 10 (Envelope), Letter, 10 x 15 cm, 13 x 18 cm, Legal
Duplex	Manual
Paper Tray Capacity	100 Sheets Standard
Media Handling	Borderless print (up to 10 x 15cm)

GENERAL

Energy Use	12 Watt (standalone copying, ISO/IEC 24712 pattern), 0.7 Watt (sleep mode), 4.3 Watt (Ready), 0.2 Watt (Power off)
Product dimensions	375 x 347 x 179 mm (Width x Depth x Height)
Product weight	3.9 kg
Compatible Operating Systems	Mac OS X 10.6.8 or later, Windows 10, Windows 7, Windows 7 x64, Windows 8 (32/64 bit), Windows 8.1, Windows 8.1 x64 Edition, Windows Server 2008 R2, Windows Server 2012 R2, Windows Server 2016, Windows Vista, Windows Vista x64, Windows XP SP3, XP Professional x64 Edition SP2
WLAN Security	WEP 64 Bit, WEP 128 Bit, WPA PSK (TKIP), WPA2 PSK (AES)
Mobile and Cloud printing services	Epson Connect (iPrint, Email Print, Remote Print Driver), Google Cloud Print
Colour	Black

OTHER

Warranty	12 months Carry in, 30,000 pages Optional warranty extension available
----------	---

LOGISTICS INFORMATION

SKU	C11CG86416CA
EAN code	8715946672939
Country of Origin	Philippines
Layer	6 Units
Layer Block	8 Units

For more information please contact:

Home users: 0343 90 37766
Business users*: 0871 42 37766
Republic of Ireland: 01 436 7742
Or visit us at <https://www.epson.co.uk/contactus>
* 10p per minute plus network extras.

Web: www.epson.co.uk
www.epson.ie

Trademarks and registered trademarks are the property of Seiko Epson Corporation or their respective owners. Product information is subject to change without prior notice.
Last extracted: 2020-04-14

EcoTank ET-2714

WHAT'S IN THE BOX

- Main unit
- Power cable
- Setup guide
- Warranty document
- 4 x 65ml individual ink bottles (Bk, C,Y,M)

INK BOTTLE COMPATIBILITY

●	104	
●	104	
●	104	
●	104	
● ● ● ●	104	

INK BOTTLE YIELD DATA



Included	3,600 pages*	6,500 pages*
Replacement	4,500 pages*	7,500 pages*

* Approx. page yield based on ISO/IEC 24711/24712 or ISO/IEC 29102/29103. Actual yield will vary depending on images printed and usage conditions. For more information visit <http://www.epson.eu/pageyield>

1. Average number of cartridges required /savings achieved printing the same number of pages using the ink bottles included within the EcoTank range, excluding hardware price. Comparison made on the average of the A4 EcoTank range versus the average of the top 10 best selling models in Western Europe, in the period January 2017– December 2017, as tracked by GfK. Printing costs calculated on the proportion of Standard and XL cartridges as tracked by GfK for the same reference period for the Western European market, using average retail prices. Ink cartridge yields as communicated by the manufacturer's websites.
2. Quoted yields are extrapolated based on Epson original methodology from the print simulation of Test Patterns provided in ISO/IEC 24712 based on the replacement ink bottles. Quoted yields are NOT based on ISO/IEC 24711. Quoted yields may vary depending on the images that you are printing, the paper type that you are using, the frequency of your prints and environmental conditions such as temperature. During the initial printer setup, a certain amount of ink is used to fill the print head's nozzles, therefore the yield of the initial bundled set can be lower.
3. Requires a wireless connection to the internet. For more information, supported languages and devices please visit www.epsonconnect.eu

EPSON®