



# ClimaSys Ventilation systems **Selection guide**


## Outlet grills

	Reference		Dimensions (mm)		IP
	RAL 7032	RAL 7035	Total (outside)	Cut-out	
	87910	87610	137 x 117	92 x 92	54
	87911	87611	170 x 150	125 x 125	54
	87912	87612	268 x 248	223 x 223	54
	87913	87613	336 x 316	291 x 291	54


## Filters

	Reference	Description	For Fans and grills dimensions (mm)
		87916	Standard filter
87917		170 x 150	
87918		268 x 248	
87919		336 x 316	
87927		"Greasy atmosphere" filter, OEMs	170 x 150
87928			268 x 248
87929			336 x 316
87924		Fine filters	170 x 150
87925			268 x 248
87926			336 x 316
87946		"Anti insect" filters	137 x 117
87947			170 x 150
87948			268 x 248
87949			336 x 316

## EMC Adapter

	Reference	For fans and grills dimensions
		87990
87991		fan 268 x 248 mm
87992		fan 336 x 316 mm
87996		grill 170 x 150 mm
87997		grill 268 x 248 mm
87998		grill 336 x 316 mm

## Stainless steel protection kit IP 55

	Reference	For fans and grills dimensions
		87937
87938		268 x 248 mm
87939		336 x 316 mm