


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0469931030](#)
Status: **Active**
Overview: Mini-Fit Family Power Connectors
Description: Mini-Fit Versa Color Plug Housing, Dual Row with Panel Mount Ears, Nylon 6/6, UL 94V-0, 10 Circuits, Glow-Wire Capable, Green

Documents:

| | |
|---|---|
| 3D Model | Packaging Specification PK-5559-001-001 (PDF) |
| Drawing (PDF) | Datasheet (PDF) |
| 3D Model (PDF) | RoHS Certificate of Compliance (PDF) |
| Product Specification PS-5556-001-001 (PDF) | |



General

| | |
|----------------|--|
| Product Family | Crimp Housings |
| Series | 46993 |
| Application | Power, Wire-to-Board, Wire-to-Wire |
| Overview | Mini-Fit Family Power Connectors |
| Product Name | Mini-Fit Versa Color |
| UPC | 195842022171 |

Physical

| | |
|-------------------------------|----------------|
| Circuits (maximum) | 10 |
| Color - Resin | Green |
| Gender | Plug |
| Glow-Wire Capable | Yes |
| Keying to Mating Part | None |
| Lock to Mating Part | Yes |
| Material - Resin | Nylon |
| Net Weight | 3.130/g |
| Number of Rows | 2 |
| Packaging Type | Bag |
| Panel Mount | No |
| Pitch - Mating Interface | 4.20mm |
| Pitch - Termination Interface | 4.20mm |
| Polarized to Mating Part | Yes |
| Temperature Range - Operating | -40° to +105°C |

Material Info

Reference - Drawing Numbers

| | |
|-------------------------|-------------------|
| Packaging Specification | PK-5559-001-001 |
| Product Specification | PS-5556-001-001 |
| Sales Drawing | SD-46993-0000-000 |

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[46993 Series](#)

Mates With

Mini-Fit Versa Color Receptacle [46992](#)

Use With

Mini-Fit Male Crimp Terminal [5558](#)