



ATXR - PROTWIST® SCREWDRIVERS FOR RESISTORX® SCREWS





Description :

- Compliant with Resistorx® specifications.
- Inline Hardening Process – +100% Tip Life and +100% Bar Strength.
- Handle Material - Softer for more Comfort and still Chemical Resistant.
- Blade " tri-coating " treatment (Zinc-Nickel-Chromium) - 4x Corrosion Resistance.
- Handle 'Channel' - +10% Torque.
- Laser Marking - gives virtually Permanent Marking.
- CNC tip machining - gives better Screw Fit increasing Torque Transfer and Reducing Wear.



References :

	A [MM]	D [MM]	D1 X L1 [MM]	L [MM]	L2 [MM]	RESISTORX [NO]	[G]
ATXR10X75	2,74	25	3,0 x 75	184	109	TT10	50
ATXR15X75	3,26	30	3,5 x 75	185	110	TT15	61
ATXR20X100	3,84	36	4,0 x 100	220	120	TT20	67
ATXR25X100	4,40	36	5,0 x 100	220	120	TT25	113
ATXR27X100	4,96	36	5,5 x 100	220	120	TT27	113

	A [MM]	D [MM]	D1 X L1 [MM]	L [MM]	L2 [MM]	RESISTORX [NO]	[G]
ATXR30X125	5,49	36	6,0 x 125	245	120	TT30	126
ATXR40X150	6,60	40	7,0 x 150	275	125	TT40	173