


## ATD.VE - PROTWIST® 1,000 VOLT INSULATED SCREWDRIVERS FOR POZIDRIV® HEAD SCREWS




### Standards :


NF ISO 8764-1, NF ISO 8764-2, NF EN 60900, ISO 8764-1, ISO 8764-2, EN 60900, DIN ISO 8764-1, DIN ISO 8764-2, DIN EN 60900, ASME B107.600

### Description :

- For improved safety, each screwdriver is tested individually at 10,000 Volt for 10 seconds VDE approved.
- Inline Hardening Process – +100% Tip Life and +100% Bar Strength.
- Handle Material - Softer for more Comfort and still Chemical Resistant.
- Handle 'Channel' - +10% Torque.
- Laser Marking - gives virtually Permanent Marking.
- CNC tip machining - gives better Screw Fit increasing Torque Transfer and Reducing Wear.



### References :

	D [MM]	D1 [MM]	E [MM]	L [MM]	L1 [MM]	L2 [MM]	L3 [MM]	POZIDRIV [NO]	[G]
ATD3X150VE	40	8,0	8,0	275	150	125	18	PZ3	195
ATD2X125VE	36	6,0	6,0	245	125	120	18	PZ2	127
ATD0X75VE	25	3,0	3,0	179	75	104	18	PZ0	46
ATD1X100VE	30	4,5	4,5	209	100	109	18	PZ1	77