


## ATD - PROTWIST® SCREWDRIVERS FOR POZIDRIV® SCREWS - ROUND BLADES




### Standards :


NF ISO 8764-1, NF ISO 8764-2, ISO 8764-1, ISO 8764-2, DIN ISO 8764-1, DIN ISO 8764-2, ASME B107.600


### Description :

- Inline Hardening Process – +100% Tip Life and +100% Bar Strength.
- Handle Material - Softer for more Comfort and still Chemical Resistant.
- Blade " tri-coating " treatment (Zinc-Nickel-Chromium) - 4x Corrosion Resistance.
- Handle 'Channel' - +10% Torque.
- Laser Marking - gives virtually Permanent Marking.
- CNC tip machining - gives better Screw Fit increasing Torque Transfer and Reducing Wear.



### References :

	D [MM]	D1 X L1 [MM]	L [MM]	L2 [MM]	POZIDRIV [NO]	[G]
ATD1X250	30	4,5 x 250	359	109	PZ1	99
ATD2X250	36	6,0 x 250	370	120	PZ2	153
ATD3X150	40	8,0 x 150	275	125	PZ3	194
ATD4X200	40	10,0 x 200	325	125	PZ4	277
ATD1X75	30	4,5 x 75	184	109	PZ1	73
ATD2X100	36	6,0 x 100	220	120	PZ2	120
ATD0X75	25	3,0 x 75	178	103	PZ0	45

	D [MM]	D1 X L1 [MM]	L [MM]	L2 [MM]	POZIDRIV [NO]	[G]
ATD1X100	30	4,5 x 100	209	109	PZ1	76
ATD2X125	36	6,0 x 125	245	120	PZ2	126