

J.10LA | J.LA - 3/8" LONG-REACH METRIC 12-POINT SOCKETS




Norm :


NF ISO 2725-1, NF ISO 1711-1, ISO 2725-1, ISO 1711-1, DIN 3124, ASME B107.5

Description :

- OGV® profile: more powerful tightening, preserves fasteners.
- Long-reach sockets for long recess or thread access.
- Available as rack sets (Ref JL.40U).
- Finish: bright chrome.



Informations :

	J.10LA
A [mm]	10
d [mm]	17,3
d1 [mm]	14,5
L [mm]	55
L1 [mm]	9,0
12-Point [mm]	12
[g]	50