

405.12MT | MICRO-TECH® "HIGH CAPACITY" CUTTERS: POWER




Norm :


NF ISO 9654, ISO 9654, DIN ISO 9654, ASME B107.500

Description :

- These pliers are suited to major efforts and repetitive work over a broad range of materials.
- Fall prevention models avoid wire ejection.



Informations :

	405.12MT
B [mm]	16
C [mm]	16
E [mm]	8
L [m]	125
L [mm]	125
Cut	h
Cu - Ni Ø [mm]	0,4 - 2,0
Fe 30 HRc diam. [mm]	1,0

	405.12MT
Piano Diameter [mm]	0,8
[g]	95