

Open Slot PVC Betaduct provides a lightweight self-extinguishing cable trunking with excellent rigidity and performance characteristics. Wide fingers give additional cable support and terminated wires can be re-routed easily. Ideal for use when bundles, cables and wires need supporting in control panels, distribution boards and switchgear. Ideal for all panel building applications.

Available in 23 sizes. Recommended fixing method; Betaduct rivets or washers. Supplied with lid.

SPECIFICATION:

- MATERIAL:** Self-Extinguishing PVC
- SLOT PITCH:** 20mm • **SLOT WIDTH:** 8mm • **WEBS:** 12mm
- COLOUR:** Black RAL 9005
- SERVICE TEMPERATURE RANGE:** -15°C to +60°C
- FLAMMABILITY:** UL94 V-0 Rated Material
- STANDARDS:** Base slots to DIN 43659. CE, RoHS, UL E161178.



PART NUMBERS:


PART NO. BLACK	NOMINAL SIZE INNER (WxH) mm	NOMINAL SIZE OUTER (WxH) mm	PACK QTY (m)
0980	19 x 50	25 x 53	24
0981	25 x 37.5	29 x 41	24
0913	25 x 50	29 x 54	24
0914	25 x 75	29 x 79	16
0983	25 x 100	30 x 105	16
0984	37.5 x 37.5	41 x 41	24
0985	37.5 x 50	41 x 54	16
0986	37.5 x 75	39 x 79	16
0987	37.5 x 100	43 x 105	16
0988	50 x 25	54 x 28	24
0989	50 x 37.5	54 x 41	16
0916	50 x 50	54 x 54	16
0917	50 x 75	55 x 79	16
0992	50 x 100	56 x 105	8
0993	75 x 37.5	80 x 41	16
0994	75 x 50	78 x 54	16
0919	75 x 75	80 x 80	16
0996	75 x 100	80 x 105	8
0998	100 x 50	107 x 54	8
0999	100 x 75	107 x 80	8
1000	100 x 100	107 x 107	8
1001	100 x 125	107 x 130	8
0941	125 x 75	131 x 78	8



Cablecraft House, Circle Business Centre, Blackburn Road, Houghton-Regis, Bedfordshire, LU5 5DD.
Phone: 01582 606033 • **Fax:** 01582 606063 • **Email:** sales@cablecraft.co.uk • **Web:** www.cablecraft.co.uk

VAT NO. GB 639 920 900 • CO. REG. NO. 2478297

PRODUCT FEATURES & BENEFITS




DON'T FORGET TO HAVE A LOOK AT OUR COMPLETE RANGE OF BETADUCT TOOLS.



PRODUCT FEATURES	PRODUCT BENEFITS
Rigid PVC Material	Self-extinguishing PVC.
Wide Finger Design	To give additional cable support. The wide fingers can be used with a range of wire and bundle sizes.
Restricted Slot Design	Saves time during installation, once wires are installed they will remain in the slot with or without cover.
Non-Slip Cover	Once installed lid will not slip. Easy clip-on assembly and disassembly.
Base Slots To DIN 43659	Staggered mounting holes, conforms to DIN standard.
Score Line At Base Of Each Slot	Fingers bend up to 90° without breaking. The score line facilitates a clean, precise break off when needed.
Smooth Round Edges	Free from burrs or sharp edges that could lead to abrasions on hands and cables.
Associated Cutting Tools - EDNT 1, EDC 1.	For clean, precise cutting of trunking fingers.

BETADUCT BASE SLOT INFORMATION



BETADUCT PVC UP TO 50MM WIDE
SINGLE BACK SLOT



TECHNICAL DATA SHEET: BETADUCT CAPACITY CHART

FILE NO. 12.2
ISSUE NO. 02

TRUNKING SIZE WIDTHxHEIGHT (mm)	CROSS SECTIONAL AREA (mm ²)	AT 55% PACKING DENSITY (mm ²)	0.50	0.75	1.00	CABLE CROSS SECTIONAL AREA (mm ²) TRI-RATED CABLE BS6231										50.00	70.00	95.00
						1.50	2.50	4.00	6.00	10.00	16.00	25.00	35.00	13.97	16.46			
			2.7	2.9	3.1	3.4	3.8	4.4	5.1	6.8	8.64	10.16	11.46					
15 x 15	225	123.75	21	18	16	13	10	8	6	3	2	1	-	-	-	-		
19 x 50	950	522.5	91	79	69	57	46	34	25	14	8	6	5	3	2	1		
25 x 20	500	275	48	41	36	30	24	18	13	7	4	3	2	1	1	1		
25 x 37.5	937.5	515.6	90	78	68	56	45	33	25	14	8	6	4	3	2	1		
25 x 50	1250	687.5	120	104	91	75	60	45	33	18	11	8	6	4	3	2		
25 x 75	1875	1031.25	180	156	136	113	90	67	50	28	17	12	9	6	4	3		
25 x 100	2500	1375	240	208	182	151	121	90	67	37	23	16	13	8	6	5		
37.5 x 37.5	1406	773.3	135	117	102	85	68	50	37	21	13	9	7	5	3	2		
37.5 x 50	1875	1031.25	180	156	136	113	90	67	50	28	17	12	9	6	4	3		
37.5 x 75	2813	1547.15	270	234	204	170	136	101	75	42	26	19	14	10	7	5		
37.5 x 100	3750	2062.5	360	312	273	227	181	135	100	56	35	25	19	13	9	7		
50 x 25	1250	687.5	120	104	91	75	60	45	33	18	11	8	6	4	3	2		
50 x 37.5	1875	1031.25	180	156	136	113	90	67	50	28	17	12	9	6	4	3		
50 x 50	2500	1375	240	208	182	151	121	90	67	37	23	16	13	8	6	5		
50 x 75	3750	2062.5	360	312	273	227	181	135	100	56	35	25	19	13	9	7		
50 x 100	5000	2750	480	416	364	303	242	180	134	75	46	33	26	17	12	10		
75 x 37.5	2813	1547.15	270	234	204	170	136	101	75	42	26	19	14	10	7	5		
75 x 50	3750	2062.5	360	312	273	273	181	135	100	56	35	25	19	13	9	7		
75 x 75	5625	3093.75	540	468	409	410	272	203	151	85	52	38	29	20	14	11		
75 x 100	7500	4125	720	624	546	547	363	271	201	113	70	50	39	26	19	15		
100 x 50	5000	2750	480	416	364	364	242	180	134	75	46	33	26	17	12	10		
100 x 75	7500	4125	720	624	546	454	363	271	201	113	70	50	39	26	19	15		
100 x 100	10000	5500	960	832	728	605	484	361	269	151	93	67	53	35	25	20		
100 x 125	12500	6875	1200	1040	910	757	606	452	336	189	117	84	66	44	32	25		
125 x 75	9375	5156.25	900	780	683	567	454	339	252	141	87	63	49	33	24	19		