



Main

Range of product	EcoStruxure operator terminal Expert
Product or component type	License
Language	French Portuguese Spanish Italian German English Chinese
Format	Paper
Previous software version	V3.0

Complementary

Range compatibility	Premium Box
Software designation	EcoStruxure Operator Terminal Expert
Type of license	Single (1 seat)
Software version	V3.1
System requirements	> 1 GB HDD storage device Windows 7 Professional 32/64 bit, > 4 GB primary memory > 1 GB HDD storage device Windows 8.1, > 4 GB primary memory > 1 GB HDD storage device Windows 10, > 4 GB primary memory > 1 GB HDD storage device Windows Embedded standard 7 32/64 bit, > 4 GB primary memory
Communication port protocol	Profibus DP slave Q series QnU CPU Ethernet Modbus TCP slave FX series Ethernet Modbus SIO ASCII master Modbus TCP master Q/QnA series serial DF1 ROC Plus SIO PacDrive ROC Plus Ethernet Ethernet/IP Uni-Telway Q series CPU direct FX series CPU direct CS/CJ series Ethernet SoMachine network

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

CANopen slave
 CS/CJ/NJ series Ethernet/IP
 Q/QnA Series Ethernet
 Modbus SIO master
 Zelio Logic
 DH485
 IQ-R/F series Ethernet
 CS/CJ series HOST link
 Simatic S7 MPI direct
 FX series computer link
 Modbus SIO slave
 Simatic S7 Ethernet
 A series Ethernet
 TIA portal Ethernet
 Controller NX1 via Ethernet/IP
 Controller NX1P via Ethernet/IP
 Controller NX7 via Ethernet/IP

Provided equipment	User's documentation in electronic format EcoStruxure operator terminal Expert
Software function	26 type of fonts 65535 alarms 65535 variables

Environment

Image import standard	PNG
-----------------------	-----

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	53 g
Package 1 Height	0.2 cm
Package 1 width	17.5 cm
Package 1 Length	25 cm
Unit Type of Package 2	S02
Number of Units in Package 2	8
Package 2 Weight	700 g
Package 2 Height	15 cm
Package 2 width	30 cm
Package 2 Length	40 cm