



STRIPLIGHTS 5050 60 | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 2607 - 2938

[View more details](#)

TECHNICAL INFORMATION

Input Power:	DC:12V
Long Life:	20,000 Hours
Body Type:	PU Glue
LED Chip Type:	SMD
Operation Temperature:	-20°C to +45°C
Dimmable:	No
Beam Angle:	120°
Color:	6400K
Dimension:	10mm
Watts per meter:	9
Lumens per meter:	1000
No. Of Led:	60/M



FEATURES

- RGB LED Strip light Kit with BS plug power adapter
- Includes 5 meter roll striplight with power adapter and remote control
- RGB Controller function: Colour changing, fading lights, flashing modes
- Flexible installation: Cutting and reconnect the strip as you wish to suit your application
- High-quality resistors for extremely lower voltage drops and efficient current control
- Standard Copper strip for excellent conductivity and heat dissipation
- Designed with 3M tape - IP65 Striplight
- Hassle free Plug and Play operation
- Suitable for illuminating borders, edges, cabinets, bars and areas with limited space for installation

CE/EMC



PACKAGING

Gross Weight (Kgs):	0.678
Unit CBM:	0.00315
Dimension:	10mm

MASTER BOX PACKAGING

Box Qty:	20
Length (Box) mm:	210
Width (Box) mm:	190
Height (Box) mm:	65

LISTING DETAILS

Commodity Code:	9405403990
EanCode:	3800157653411