



TECHNICAL INFORMATION

Watts:	15
Lumens:	1400
Shape:	Round
Input Power:	AC:200-240V, 50/60Hz
Long Life:	30,000 Hours
Unit Color:	White
Body Type:	PC
LED Chip Type:	SMD-Samsung Chip
CRI:	>80
Operation Temperature:	-20°C to +45°C
Dimmable:	No
Beam Angle:	120°
Color:	3000K
Dimension:	Ø320x100mm
Sensor Type:	Microwave
Detection Distance:	3-6m


BULKHEAD SENSOR | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 803 - 1281 940

[View more details](#)



IP65
RATING



5 YEAR
WARRANTY



IK 08



CRI > 80



SAVE UP TO
85%
ENERGY

FEATURES

- Fitted with high efficiency Samsung LED Chips that offer up to 85% in energy savings
- These IP65 LED bulkheads are equipped with microwave sensor featuring corridor function, day light sensor, dimmable function and many more
- DIP switch sensor setting allowing flexible sensor settings
- 120° / 360° Detection Angle
- 0.5~3m/s Detection Motion Speed
- Suitable for open areas constantly exposed to dust and moisture like parking lots, corridors, airports, and malls

CE/EMC

CE/LVD



PACKAGING

Gross Weight (Kgs):	1.13
Unit CBM:	0.011979
Dimension:	Ø320x100mm

MASTER BOX PACKAGING

Box Qty:	10
Qty Per Pallet:	230
Length (Box) mm:	110
Width (Box) mm:	330
Height (Box) mm:	330

LISTING DETAILS

Commodity Code:	9405403990
EanCode:	3800157636483