



TECHNICAL INFORMATION

Watts:	15
Lumens:	1400
Shape:	Round
Input Power:	AC:200-240V, 50/60Hz
Long Life:	30,000 Hours
Unit Color:	White
Body Type:	PC
LED Chip Type:	SMD-Samsung Chip
CRI:	>80
Operation Temperature:	-20°C to +45°C
Dimmable:	No
Beam Angle:	120°
Color:	6400K
Dimension:	Ø320x100mm
Sensor Type:	Microwave
Detection Distance:	3-6m


BULKHEAD SENSOR | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 805 - 1281 940

[View more details](#)



FEATURES

- Fitted with high efficiency Samsung LED Chips that offer up to 85% in energy savings
- These IP65 LED bulkheads are equipped with microwave sensor featuring corridor function, day light sensor, dimmable function and many more
- DIP switch sensor setting allowing flexible sensor settings
- 120° / 360° Detection Angle
- 0.5~3m/s Detection Motion Speed
- Suitable for open areas constantly exposed to dust and moisture like parking lots, corridors, airports, and malls

CE/EMC

CE/LVD



PACKAGING

Gross Weight (Kgs): 1.13
Unit CBM: 0.011979
Dimension: Ø320x100mm

MASTER BOX PACKAGING

Box Qty: 10
Qty Per Pallet: 100
Length (Box) mm: 330
Width (Box) mm: 330
Height (Box) mm: 110

LISTING DETAILS

Commodity Code: 9405403990
EanCode: 3800157636506