



TECHNICAL INFORMATION

Input Power:	AC:100-240V, 50/60Hz
LED Chip Type:	SMD 5050
Beam Angle:	120°
Color:	RGB
Watts per meter:	4.8
Lumens per meter:	500
Current per meter:	0.4A
Roll Qty:	10M

STRIPLIGHT KITS BS PLUG | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 2631 - 2938

[View more details](#)



FEATURES

- LED RGB Strip Light Kit with Power adaptor and Dual Output IR Controller
- Plug and Play without any hassles and trouble
- Color changeable via remote control
- 2X5 Meter roll with BS Plug type
- Suitable for illuminating borders, edges, cabinets, bars and areas with limited space for installation



PACKAGING

Gross Weight (Kgs): 0.81
Unit CBM: 0.00383

MASTER BOX PACKAGING

Box Qty: 20
Length (Box) mm: 210
Width (Box) mm: 190
Height (Box) mm: 80

LISTING DETAILS

Commodity Code: 9405403990
EanCode: 3800157658195