

PRODUCT DATASHEET

LinearLED Mobile Battery 300

Linear LED Mobile | Undercabinet luminaire for flexible mounting, with motion sensor, battery-powered



AREAS OF APPLICATION

- For a very large range of uses
- For indoor use only
- Shelves, furniture integration or under cabinet mounting

PRODUCT BENEFITS

- Attractive and functional design
- Economical operation due to low power consumption
- Easy and quick installation

PRODUCT FEATURES

- Housing material: aluminum
- Integrated light and motion sensor
- Switch for Auto- or On/Off-Mode



TECHNICAL DATA

Electrical data

Nominal wattage	2.90 W
Nominal voltage	9 V
Mains frequency	0 Hz

Photometrical data

Color temperature	4000 K
Color rendering index Ra	>80
Light color (designation)	Cool White
Luminous flux	174 lm
Luminous efficacy	60 lm/W


Light technical data

Beam angle	120 °
------------	-------

Luminaire sensor data

Type of sensor	Motion
Sensor technology	Passive infrared (PIR)

Dimensions & weight



Length	314.0 mm
Width	48.0 mm
Height	18.0 mm
Product weight	368.00 g

Colors & materials

Body material	Aluminum
Product color	White

Housing color	White
----------------------	-------

Temperatures & operating conditions

Ambient temperature range	-20...+40 °C
----------------------------------	--------------

Lifespan

Number of switching cycles	12500
Lifespan	25000 h

Additional product data

Mounting type	Surface
Mounting location	Cabinet undersides

Capabilities

Dimmable	No
LED module replaceable	Not replaceable

Certificates & standards

Protection class	III
Type of protection	IP20
Standards	CE/EAC/REACH/RoHS

EQUIPMENT / ACCESSORIES

- Batteries included: 4x 1.5 V LR6 (AA)
- All required accessories included

LOGISTICAL DATA

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4058075226883	Blister 1	22 mm x 140 mm x 400 mm	416.00 g	1.23 dm ³
4058075226890	Shipping carton box 6	413 mm x 161 mm x 158 mm	2660.00 g	10.51 dm ³
4058075226906	Shipping carton box 36	500 mm x 430 mm x 330 mm	16539.00 g	70.95 dm ³

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.