

TECHNICAL DATA

[page2](#)

Model Number: MC090D050UK/F+
Type: Single--Voltage AC/DC Adaptor

Electrical Data

| | | |
|-------------------|----------------------------|--|
| Input | Input Voltage/Frequency | 230V/50Hz |
| | Input Power | 11.2W |
| Output | Rated Output Voltage | 9V |
| | Rated Output Load Current | 500mA |
| | Rated Output Power | 4.5 VA |
| Resistance | Insulation Resistance | 100MΩ(measured with 500V DC voltage) |
| Protection | Thermal Protection | Thermal fuse:125□/2A |
| | Withstand Voltage (Hi-Pot) | AC 3750V 50Hz for 1minute or AC4000V 2seconds |

Mechanical Data

| | |
|------------------------------|-----------------|
| Supply Connection Type | UK |
| Primary Turns & Wire Gauge | 2050T/0.11mm |
| Secondary Turns & Wire Gauge | 94T/0.45mm |
| Core Size | 41mm×26mm |
| Output Plug Dimensions | 5.0X2.5X12mm |
| Polarity | CENTRE POSITIVE |
| Unit Weight | 242g |
| Dimensions | 67×50×72(mm) |