

# DYMO®

## LabelManager™ 420P



### CREATE LABELS FAST WITH SMART KEYS

High-performance label maker allows you to print barcodes or customized labels with own fonts and graphics.


#### Features

- Large, 4-Line backlit display
- Long lasting rechargeable battery pack
- PC or MAC® connectivity with DYMO® Connect
- 30+ ways to format texts
- Print upto 10 copies of the same labels
- Save upto 15 frequently used labels
- Print Barcodes - UPC-E, Code 39, Code 128, EAN13, EAN8, UPC-A
- Print upto 3/4 in (19mm) wide labels
- For even more features, download DYMO® Connect



#### Single Unit Includes:

- LabelManager 420P
- Rechargeable Lithium-Ion Battery
- D1 Starter Label Cassette, 19mm x 3m Black on White
- Charging Adapter
- USB Cable
- Quick Start Guide
- 2 + 1 - Year Limited Warranty\*



#### Kit Includes:

- LabelManager 420P + Softcase Bag
- Rechargeable Lithium-Ion Battery
- 4 x D1 Label Cassettes, 6mm x 7m Black on Clear | 9mm x 7m Black on Yellow | 12mm x 7m Black on White | 19mm x 7m Black on Red
- Charging Adapter
- USB Cable
- Quick Start Guide
- 2 + 1 - Year Limited Warranty\*



#### Quick Specs

Unit Dimensions (H x W x L)	104 x 215 x 57 mm
Weight (excluding battery)	415 g
Mac®/PC Compatible	Yes via DYMO® Connect
Accepts Label Sizes	6mm, 9mm, 12mm and 19mm
Tape Platform	D1, Durables
Resolution	180 dpi
Printing System	Thermal Transfer
Print Speed	12 mm/sec
Barcodes	Yes
Cutter Type	Manual
Batteries	Rechargeable
Adapter	Yes (included)
Networking	No
Country of Origin	China

Item Number	Description	Length (cm)	Width (cm)	Height (cm)	QTY	EAN	Customer Price
S0915490	LabelManager 420P ABC	10.0	18.7	25.0	1	3501170915493	
S0915480	LabelManager 420P ABC KIT	26,5	104.0	57.0	1	3501170915486	
<b>Accessories (www.dymo.com)</b>							
S0895890	Charging Adapter	9.0	4.8	8.2	-	-	

\* +1 year if registered on the DYMO® website



100% recycled material used for external cassette



+40% of DYMO® labels are produced\* using „Water based solvents“.




DYMO® high quality labels are made in Belgium



## D1 Standard Polyester Labels

For hundreds of tasks around the office or home office, such as filing, storage and asset tracking.  
Temperature rating: -18°C to 90°C


D1 STANDARD LABELS (7 m)	6 mm	9 mm	12 mm	19 mm
ABC	S0720780	S0720680	S0720530	S0720830
ABC	S0720770	S0720670	S0720500	S0720820
ABC	S0720790	S0720730	S0720580	S0720880
ABC	-	S0720710	S0720560	S0720860
ABC	-	S0720740	S0720590	S0720890
ABC	-	S0720720	S0720570	S0720870
ABC	-	-	S0720610	S0720910
ABC	-	S0720690	S0720540	S0720840
ABC	-	-	S0720510	-
ABC	-	-	S0720600	-
ABC	-	S0720700	S0720550	S0720850
ABC	-	-	S0720520	-
D1 STANDARD MULTIPACKS (7 m)	6 mm	9 mm	12 mm	19 mm
ABC	-	2093096	2093097	2093098



## D1 Durable Vinyl Labels

Industrial strength adhesive helps to ensure labels stay stuck to a variety of surfaces.  
Temperature rating: -40°C to 80°C

D1 DURABLE LABELS (3 m)	12 mm
ABC	1978366
ABC	1978365
ABC	1978367
D1 DURABLE LABELS (5.5 m)	12 mm
ABC	1978364



## D1 Permanent Polyester Labels

Professional, polished finish ideal for panels, blocks, faceplates, shelves, bins and more.  
Temperature rating: -40°C to 150°C\*

D1 PERMANENT POLYESTER (5.5 m)	12 mm	19 mm
ABC	S0718060	S0718050


\*depends on surface



## D1 Flexible Nylon Labels

Specifically designed for curved surfaces and wire and cable marking.  
Temperature rating: -40°C to 60°C

D1 FLEXIBLE NYLON (3.5 m)	12 mm	19 mm
ABC	S0718040	S0718070



The DYMO® high quality labels are made in Belgium



© 2021 Newell Brands

This information is being provided for general information purposes and the compliance standards and certifications referenced herein are based on current standards which are subject to change.

