

WorkForce WF-2850DWF



Compact 4-in-1 inkjet printer designed for home and small offices with ADF, large LCD screen, Wi-Fi and mobile printing.

This stylish, compact and easy-to-use 4-in-1 inkjet printer can reduce waste and costs with A4 double-sided printing and affordable individual inks. Speed through multi-page copying, scanning and faxing with the Automatic Document Feeder (ADF) and the large 6.1cm LCD screen. Printing on the go is easy with Wi-Fi, Wi-Fi Direct and mobile printing apps and utilise scan-to-cloud.

Compact and stylish

With its sleek and refined form, it's easy to integrate this space-saving, 4-in-1 model into any home office.

Easy to use

On the spot the printer's functions can be easily navigated thanks to the intuitive user interface and large LCD screen. Speed through tasks using the 30-page ADF (Automatic Document Feeder) for multi-page scanning, copying and faxing with minimal effort. Save paper and money with A4 double-sided printing.

Affordable solution

Epson's four-colour 603 inks provides reliable, vibrant and clear prints with minimal outlay. Each colour is supplied individually, so you only replace the colours you need. This makes individual inks 50% more efficient compared to tri-colour cartridges¹. Reduce costs even further with Epson's XL cartridges, that can print 2.5x more pages².

Go wireless


With Wi-Fi and Wi-Fi Direct, you can send documents to print from smart devices using the Epson iPrint³ app. It can even receive files from almost anywhere in the world via Epson Email Print¹. You can also store or share documents online by scanning directly to cloud storage sites³.

DATASHEET / BROCHURE



KEY FEATURES

- **Wi-Fi 4-in-1**
Print, scan, copy and fax
- **Business features**
ADF, business-quality documents and A4 double-sided printing
- **Easy mobile printing and scanning**
Print easily from your smartphone or tablet and utilise scan-to-cloud³
- **Individual inks**
Save money by only replacing the colour used
- **6.1cm LCD screen**
Easily navigate through the printer's functions



PRODUCT SPECIFICATIONS

TECHNOLOGY

Printing Method	4-colour inkjet printer
Minimum Droplet Size	3.3 pl, With Variable-Sized Droplet Technology
Ink Technology	Pigment black and Dye colour Inks

PRINT

First Page Out	Monochrome 10 Seconds, Colour 16 Seconds, According to IEEE/ISO 17629
Printing Speed ISO/IEC 24734	10 pages/min Monochrome, 5 pages/min Colour
Duplex Printing Speed ISO/IEC 24734	6 A4 Pages/min Monochrome, 4 A4 Pages/min Colour
Maximum Printing Speed	18 pages/min Colour (plain paper 75 g/m ²), 33 pages/min Monochrome (plain paper 75 g/m ²)
Printing Resolution	5,760 x 1,440 DPI
Printing Volume	3,000 pages per month The maximum number of printed pages per month based on the performance capabilities of the printer, including ISO rated print speeds and paper handling capabilities.

Colours Black, Cyan, Yellow, Magenta
For detailed information on printing speeds please visit <http://www.epson.eu/testing>.

SCAN

Optical Resolution	1,200 DPI x 2,400 DPI (Horizontal x Vertical)
Output formats	BMP, JPEG, TIFF, multi-TIFF, PDF, PNG
Scanner type	Contact image sensor (CIS)

FAX

Fax speed dials (max)	60 names and numbers
Page memory	Up to 100 pages (ITU-T No.1 chart)
Fax Functions	PC Fax, Memory Reception, Auto Redial, Speed Dial

PAPER / MEDIA HANDLING

Paper Formats	No. 10 (Envelope), DL (Envelope), C6 (Envelope), B5 (17.6x25.7 cm), A6 (10.5x14.8 cm), A5 (14.8x21.0 cm), A4 (21.0x29.7 cm), Letter, Letter Legal, 10 x 15 cm, 13 x 18 cm, 16:9, User defined
Automatic Document Feed	30 pages
Duplex	Yes (A4, plain paper)
Paper Tray Capacity	100 Sheets Standard
Number of paper trays	1

CONNECTIVITY

Interfaces	Wi-Fi Direct, Wireless LAN IEEE 802.11b/g/n, Hi-Speed USB - compatible with USB 2.0 specification
WLAN Security	WEP 64 Bit, WEP 128 Bit, WPA PSK (TKIP), WPA PSK (AES)

GENERAL

Energy Use	4.2 Watt (Ready), 0.2 Watt (Power off), 14 Watt (standalone copying, ISO/IEC 24712 pattern), 1.3 Watt (sleep mode)
------------	--

OTHER

Warranty	12 months Carry in Optional warranty extension available
----------	---

LOGISTICS INFORMATION

SKU	C11CG31401
EAN code	8715946665290
Country of Origin	Indonesia
Layer	4 Units
Layer Block	6 Units

For more information please contact:

Home users: 0343 90 37766
Business users*: 0871 42 37766
Republic of Ireland: 01 436 7742
Or visit us at <https://www.epson.co.uk/contactus>
* 10p per minute plus network extras.

Web: www.epson.co.uk
www.epson.ie

Trademarks and registered trademarks are the property of Seiko Epson Corporation or their respective owners.
Product information is subject to change without prior notice.
Last extracted: 2020-09-25

WorkForce WF-2850DWF

WHAT'S IN THE BOX

- Main unit
- Individual Ink Cartridges
- Warranty document
- Software (CD)
- Power cable
- Setup guide

INK CARTRIDGE COMPATIBILITY



INK YIELD DATA

	Starfish 603	Starfish 603XL
●	150 pages*	500 pages*
● ● ●	130 pages*	350 pages*

* Approx. page yield based on ISO/IEC 24711/24712 or ISO/IEC 29102/29103. Actual yield will vary depending on images printed and usage conditions. For more information visit <http://www.epson.eu/pageyield>

1. Based on testing carried out by BLI in July 2019, compared to equivalent competitor (HP and Canon) printer models, using tri-colour cartridges, according to the manufacturers' websites, July 2018. Weighting for Document and Photo printing applied based on TNS 'Printing Usage & Attitudes Study', June 2013.

2. Epson iPrint and Epson Creative Print require a wireless connection and the Epson printing apps. Epson Email print, Epson Remote Print Driver and Epson scan-to cloud require an internet connection. For more information, supported languages and devices, please visit www.epsonconnect.eu

3. For more information, please visit www.epson.eu/pageyield

EPSON[®]