




Quality Products. Service Excellence.

Fan Top Panel C2TF Series

Features



- Use with **C2, C2RR, C4, C4RR, H1** or **CLC** cabinet series.
 - H1 requires H1TC Series for mounting.
- 14 gauge steel construction.
- cURus Recognized to UL507 and CSA C22.2 No.113.

Fan Tops for use with 4" Fans:

- 4" fan top panel - fans not included (see first table below).
- 4 or 6 opening depending on depth of rack.
- Maximum flexibility - add fans OR leave holes open (for cable access) OR use covers (see below) OR any combination.



Pre-Wired Fan Tops:

- Available with (4) 4" fans or (1) 10" fan (factory wired).
- Long life, ball bearing, 4", 115 volt, 50/60 Hz. AC fan(s).
- Available in three depths and two colors.
- 4.7" versions are available with or without adjustable thermostats.
- 10" versions are available with or without cable entry holes.



Accessories

- Tube Axial Fans
- Filter Fan Grills
- Metal Fan Guard

Part No. Black	Part No. Light Gray	Description	Fan Quantity	Fan Size	CFM	dB	Thermostat Included	Cable Entry
C2T1923FBK1	C2T1923FLG1	Cutout for Fan or Cable Entry	4 (Opening Only)	4.70	-	-	No	Optional
C2T1931FBK1	C2T1931FLG1	Cutout for Fan or Cable Entry	6 (Opening Only)	4.70	-	-	No	Optional
C2T1936FBK1	C2T1936FLG1	Cutout for Fan or Cable Entry	6 (Opening Only)	4.70	-	-	No	Optional
C2T2423FBK1	C2T2423FLG1	Cutout for Fan or Cable Entry	4 (Opening Only)	4.70	-	-	No	Optional
C2T2431FBK1	C2T2431FLG1	Cutout for Fan or Cable Entry	6 (Opening Only)	4.70	-	-	No	Optional
C2T2436FBK1	C2T2436FLG1	Cutout for Fan or Cable Entry	6 (Opening Only)	4.70	-	-	No	Optional
C2T1923VFBK1	-	Fan Grill for Fan or Venting	4 (Fan Grill Only)	4.70	-	-	No	No
C2T1931VFBK1	-	Fan Grill for Fan or Venting	6 (Fan Grill Only)	4.70	-	-	No	No
C2T1936VFBK1	-	Fan Grill for Fan or Venting	6 (Fan Grill Only)	4.70	-	-	No	No
C2T2423VFBK1	C2T2423VFLG1	Fan Grill for Fan or Venting	4 (Fan Grill Only)	4.70	-	-	No	No
C2T2431VFBK1	C2T2431VFLG1	Fan Grill for Fan or Venting	4 (Fan Grill Only)	4.70	-	-	No	No
C2T2436VFBK1	C2T2436VFLG1	Fan Grill for Fan or Venting	6 (Fan Grill Only)	4.70	-	-	No	No
C2T1923F10BK1	C2T1923F10LG1	Pre-Wired Fan	1	10.00	550	60	No	No
C2T1931F10BK1	C2T1931F10LG1	Pre-Wired Fan	1	10.00	550	60	No	No
C2T1936F10BK1	C2T1936F10LG1	Pre-Wired Fan	1	10.00	550	60	No	No
C2T2431F10BK1	C2T2431F10LG1	Pre-Wired Fan	1	10.00	550	60	No	No
C2T2436F10BK1	C2T2436F10LG1	Pre-Wired Fan	1	10.00	550	60	No	No

Part No. Black	Part No. Light Gray	Description	Fan Quantity	Fan Size	CFM	dB	Thermostat Included	Cable Entry
C2T1923F10CEBK1	C2T1923F10CELG1	Pre-wired fan with cable entry grommets	1	10.00	550	60	No	Yes
C2T1931F10CEBK1	C2T1931F10CELG1	Pre-wired fan with cable entry grommets	1	10.00	550	60	No	Yes
C2T1936F10CEBK1	C2T1936F10CELG1	Pre-wired fan with cable entry grommets	1	10.00	550	60	No	Yes
C2T2423F10CEBK1	C2T2423F10CELG1	Pre-wired fan with cable entry grommets	1	10.00	550	60	No	Yes
C2T2431F10CEBK1	C2T2431F10CELG1	Pre-wired fan with cable entry grommets	1	10.00	550	60	No	Yes
C2T2436F10CEBK1	C2T2436F10CELG1	Pre-wired fan with cable entry grommets	1	10.00	550	60	No	Yes
C2T1923F4BK1	C2T1923F4LG1	Pre-wired fans	4	4.70	400	64	No	No
C2T1931F4BK1	C2T1931F4LG1	Pre-wired fans	4	4.70	400	64	No	No
C2T1936F4BK1	C2T1936F4LG1	Pre-wired fans	4	4.70	400	64	No	No
C2T2431F4BK1	C2T2431F4LG1	Pre-wired fans	4	4.70	400	64	No	No
C2T2436F4BK1	C2T2436F4LG1	Pre-wired fans	4	4.70	400	64	No	No
C2T1923F4TBK1	C2T1923F4TLG1	Pre-wired fans with thermostat	4	4.70	400	64	Yes	No
C2T1931F4TBK1	C2T1931F4TLG1	Pre-wired fans with thermostat	4	4.70	400	64	Yes	No
C2T1936F4TBK1	C2T1936F4TLG1	Pre-wired fans with thermostat	4	4.70	400	64	Yes	No
C2T2423F4TBK1	C2T2423F4TLG1	Pre-wired fans with thermostat	4	4.70	400	64	Yes	No
C2T2431F4TBK1	C2T2431F4TLG1	Pre-wired fans with thermostat	4	4.70	400	64	Yes	No
C2T2436F4TBK1	C2T2436F4TLG1	Pre-wired fans with thermostat	4	4.70	400	64	Yes	No

Cabinet Compatibility

Cabinet Size	C2 Cabinet		C4 Cabinet		DCZ4 Cabinet		H1 Cabinet	RCK Cabinet
	Width	Depth	Width	Depth	Width	Depth		
1923	23	23.63	24	31.5	-	-	All Sizes	All Sizes
1931	23	31.5	24	36	-	-	-	-
1936	23	36	24	42	-	-	-	-
2423	-	-	30	31.5	-	-	-	-
2431	-	-	30	36	30	42	-	-
2436	-	-	30	42	-	-	-	-

Fan Cover Plate

Part No.	DNFPBK1
----------	---------

Individually packaged 4 inch hole cover (hardware included)

Data subject to change without notice

© 2021. Hammond Manufacturing Ltd. All rights reserved.