

363154

Supplier		
Model number	GSB 90-2E	8406
Input power (W)	1150	850
No load speed (rpm)	0-700/0-2100	0-1500
Drilling capacity steel (mm)	16	13
Drilling capacity masonry (mm)	32	20
Maximum diamond core (mm)	90	152
Weight (kg)	4.0	3.5
Order code (230V)	055-202	138-2584
Order code (110V)	055-203	138-2586
Price		
each		