


Part Number: 1831035X

Type	Size	Rating	Description
LED	T10	24VDC	10mm Bayonet MultiLED



Part #	Colour	Voltage(VDC)	Current(mA)	Intensity(mcd)
18310350	Red	24	14	50
18310351	Green	24	14	90
18310352	Yellow	24	14	60

Notes:

- 1 **Base Type** BA9s/13 Nickel plated BS EN 60061-1
- 2 **General**
 - Storage temperature -25 °C to +80°C
 - Application temperature -20 °C to +60°C
 - Voltage tolerance ±10%
 - Due to component tolerances, colour temperature variations may be observed
 - The plastic(polycarbonate) has limited chemical resistance
- 3 **Environmental** RoHS & REACH SVHC compliant