


Part Number: 1512135X

Type	Size	Rating	Description
LED	T6	24VDC	Midget Groove 6-chip



Part No.	Colour	Current (mA)	Intensity (mcd)
15121350	Red	14 nom	40 nom
15121351	Green	14 nom	50 nom
15121352	Yellow	14 nom	35 nom
15121353	Ultra-red	14 nom	50 nom
15121354	Red/Green	14 nom	40/50 nom
15121356	Ultra-yellow	14 nom	50 nom

Notes:

- 1 Electrical & optical data are measured at an ambient temperature of 25°C
- 2 Storage temperature -25 °C to +80°C
- 3 Application temperature -20 °C to +60°C
- 4 Voltage tolerance ±10%
- 5 Due to component tolerances, colour temperature variations may be observed
- 6 The plastic (polycarbonate) has limited chemical resistance
- 7 RoHS & REACH SVHC compliant