


Part Number: 1920X000

Type	Size	Rating	Description
LED	M8	-	LED Infra-Red Panel Indicator

Dimensions (mm)



Wavelength	Voltage	Current (mA)	Intensity (mcd)
940nm	1.3Vdc	30mA max.	7.2mW/sr @ 20mA

Notes:

- 1 Electrical & optical data are measured at an ambient temperature of 25°C
- 2 Storage temperature -25 °C to +80°C
- 3 Application temperature -20 °C to +60°C
- 4 Sealed to IP67 above panel when supplied gasket used
- 5 RoHS & REACH SVHC compliant