


Part Number: **CM1819**

Type	Size	Rating	Description
Incandescent	T10	28V 40mA	T-3¼ Miniature bayonet Lamp



Dimensions in millimetres

TEST VOLTS	CURRENT (mA)			LIGHT OUTPUT (Lm)			LIFE Hours
	Min.	Nom.	Max.	Min.	Nom.	Max.	
28	36	40	44	3.2	4.3	5.4	1,000

Notes:

- 1 **Base Type** BA9s/13 in accordance with EN 60061-1
- 2 **Filament Shape** C-2F
- 3 **Lamp Marking** CM1819 with or without rating
- 4 **Bead colour** White or clear
- 5 **LCL** 16 ± 1 mm.
- 6 **Environmental** RoHS & REACH SVHC compliant