


Part Number: 1511AX5XX

Type	Size	Rating	Description
LED	T5	AC/DC	T-1½ Wedge base



Part #	Colour	Voltage (V)	Current (mA)	Intensity (mcd)
1511A25W3A	White clear	12	8	2600
1511A25W3DA	White diffuse	12	8	1400
1511A35W3A	White clear	24	9	3000
1511A35W3DA	White diffuse	24	9	1600
1511A45W3A	White clear	28	9	3000
1511A45W3DA	White diffuse	28	9	1600

Notes:

- 1 Electrical & optical data are measured at an ambient temperature of 25°C
- 2 Storage temperature -25 °C to +80°C
- 3 Application temperature -20 °C to +60°C
- 4 Voltage tolerance ±10%
- 5 Due to component tolerances, colour temperature variations may be observed
- 6 The plastic (polycarbonate) has limited chemical resistance
- 7 RoHS & REACH SVHC compliant