

Supplier			
Model number	RP1110 C	3612	3612C
Input power (W)	1100	1650	1850
No load speed (rpm)	8000-24000	22000	9000-23000
Tool holder	8mm + 6.35mm	1/2in	1/2in
Maximum plunge depth (mm)	57	60	60
Weight (kg)	2.4	5.8	6.0
Order code (230V)	138-2532	138-2504	138-2589
Order code (110V)	138-2533	138-2505	138-2590
Price each			

363230