

Flute geometry

Standard helix, right hand spiral

Point angle

118°

Surface treatment


Blue

Range

13 - 25mm, 17/32 - 1 1/4in

Application

For general purpose light duty work only. Fracturing of the drill shank may occur if it is used for any other purpose or if extreme pressure is exerted on the drill.

**Metric**

Size (mm)	Flute length (mm)	Overall length (mm)	Order code	Price each
13	83	156	No Order Code	
14	83	156	138-9512	
15	83	156	No Order Code	
16	84	157	No Order Code	
16.5	84	157	No Order Code	
17	84	157	No Order Code	
18	84	157	No Order Code	
19	84	157	No Order Code	
20	81	158	No Order Code	
21	82	158	No Order Code	
22	82	158	No Order Code	
23	82	158	No Order Code	
24	83	159	No Order Code	
25	83	159	No Order Code	

Fractional

Size (in)	Flute length (mm)	Overall length (mm)	Order code	Price each
17/32	84	157	No Order Code	
9/16	83	156	No Order Code	
5/8	83	156	No Order Code	
11/16	84	157	No Order Code	
3/4	84	157	No Order Code	
13/16	82	158	No Order Code	
7/8	83	159	No Order Code	
15/16	83	159	No Order Code	
1	83	160	No Order Code	
1 1/4	85	161	No Order Code	