



### 32" HD LED Digital TV

- 32" HD Ready widescreen LED TV
- Built-in Freeview T2 HD and Digital Freeview Channels
- HDMI input for your external devices and consoles
- Can be wall mounted (100mm x 100mm)

		<b>EAN</b>	<b>5060062269819</b>
<b>Specifications</b>	Model No.	C3220DVB	
	Chipset	MSD3663	
	Sales Market	England	
	VESA Size	100 x 100	
	Wall Mount Screws	M5 x 8	
	Speaker Output	2 x 8W	
	Actual Size of Display (Diagonal)	31.5"	
<b>Display</b>	Display Type	LED	
	Resolution	1366 x 768 (16:9)	
	Brightness (nit)	200	
	Contrast	3000:1	
	Display Colours	16.7M	
	Refresh Rate	60Hz	
	Viewing Angle H/V	178/178	
<b>Accessories</b>	Remote	1	
	Battery	AAA x 2	

Terminals		
	HDMI Input	2
	RCA Component + AUDIO Input	1
	RCA Composite + AUDIO Input	1
	12-PIN VGA + AUDIO Input	1
	RF Input	1
	Optical Digital AUDIO Input	1
	Coaxial Digital AUDIO Input	0
	Analog AUDIO Output	0
	3.5mm Headphone Output	1

Features		
	DVD	No
	DVB-S	Without
	DVB-S2	Without
	DVB-T+C	With
	DVB-T2+C	With
	CI	With
	3D Digital Comb Filter + 3D Noise Reduction	Yes
	Automatic Volume Control	Yes
	Sleep Timer	Yes
	NO Signal Shut Down	Yes
	Adjustable Bass & Treble Controls	Yes
	Adjustable Balance Control	Yes
	Picture Modes	Standard/Dynamic/Soft/User
	Preset Sound Modes	Standard/Music/Movie/User
	OSD Menu Language	English/French/Spanish/Italy/Germany/Portugal
	Aspect Ratio Modes	Wide/Zoom/Cinema/Normal
	PVR Function	Recording standby, time-shift EPG recording reservation

Power		
	Power Supply	AC 100V-240V - 50Hz/60Hz
	Operation Power Consumption	34W
	Max Power Consumption	60W
	KWh/annum	50kWh
	Standby Consumption	<0.5W
	Energy Efficiency Class	A

Dimensions		
	Unit Dimensions w Stand	730.26 x 468.88 x 195.29
	Unit Dimensions w/o Stand	730.26 x 430.76 x 94
	Carton Box Dimensions	
	Weight (Kg)	4.3