



16" Full HD LED Digital with built-in DVD Player & Satellite Tuner

- 16" Full HD widescreen LED TV
- Built-in DVD Player
- Built-in satellite tuner
- HDMI input for your external devices and consoles
- Can be wall mounted (75mm x 75mm)

	EAN	5060062268423
Specifications	Model No.	C1620FS
	Chipset	MSD3663
	Sales Market	UK
	VESA Size	75 x 75
	Wall Mount Screws	M4 x 8
	Speaker Output	2 x 3w
	Actual Size of Display (diagonal)	15.6"
Display	Display Type	LED
	Resolution	1920 x 1080
	Brightness (nit)	200
	Contrast	700:1
	Display Colours	26.2K
	Viewing Angle(L/R/U/D)	85/85/85/85(CR≥10)
	DVD	YES
DTV System	TV Solution	Mstar3663
	TV System	ATV: PAL BG/DK/ SECAM BG/DK/L/L' DTV:DVB-T & DVB-C & DVB-S2&DVBT2, MPEG 2,MP@ML, MPEG 4
	TV Band	ATV 49MHz - 863MHz, DTV VHF (174MHz-- 230MHz), UHF (474MHz-- 862MHz)
	Video System	MPEG 2 MP@HL, MPEG-2, MP@HL, H.264
	Tuning System	FST
	Number of channel for storing	100 Analog / 400 Digital

Accessories	Remote	1
	Battery	AAA x 2

Terminals	HDMI Input	x 1
	CVBS	x 1
	PC In	x 1
	USB	x1

Features	DVD Loader	FORYOU
	DVD Solution	MTK-MTK1389
	DVD/DVD-R/DVD+R/DVD-RW/DVD+RW/CD/MP3/JPEG playback	YES
	DVD Reverse Play	YES
	Skip Forward/Reverse	YES
	DVD Multi-Speed Scan/Slow	YES
	Slot-Load Type Vertical Play DVD Mechanism	YES
	APS	ATV, DVBT, DVBC storage in capture order
	OSD Language	English, Deutsch, Francais, Espanol, Portugese, Italian.
	EPG (Electronic Program Guide)	7 days
	Automatic Tuning	YES
	Sleep Timer	YES (240min)
	Color Temperature Adjustment	YES
	Picture Mode	Standard / Dynamic / Mild / User
	Home Mode	YES
	Hotel mode	YES

Power	Power supply	DC12V-2A /AC 100V-240V~ 50Hz/60Hz
	Energy efficiency rating	A
	Operation power consumption	14W
	Max power consumption	24W
	Stand by power consumption	<0.5W

Dimension	Unit Dimensions w Stand	374 x 120 x 274
	Unit Dimensions w/o Stand	374 x 48 x 244
	Carton Box Dimensions	433 x 314 x 120
	Weight (Kg)	1.7