

WorkForce WF-7210DTW



Take advantage of this high quality, cost-effective A3 inkjet, with dual paper trays, double-sided printing and wireless connectivity options.

Get professional-looking prints quickly and without breaking the bank with the high quality WF-7210DTW. Workflows become smoother and more efficient through fast print speeds and dual paper trays. With costs slashed thanks to individual inks and a suite of flexible wireless solutions freeing you to work where and how you want, it's sure to impress.

Professional A3 printing

This A3 printer will meet the needs of even the most demanding home office and small office users. It can handle double-sided printing up to A3 and features two paper trays, which are ideal for alternating between different media. Furthermore, its PrecisionCore printhead produces high-quality, laser-like prints.

Enhance your productivity

This efficient, reliable and fast model offers A3 double-sided printing and print speeds of 18ppm in black and 10ppm in colour¹. It's simple to operate directly thanks to its easy-to-use 5.6cm LCD screen.

Minimise your outgoings

Dramatically reduce your costs; this printer offers up to 50 percent lower cost-per-page than competitors' laser models². Its inks are very economical; they're supplied individually, so you only replace the colour used. Giving great value for money, cartridges are available in standard, XL and XXL, with the highest yield delivering up to 2,200 pages³.

Flexible wireless solutions


Print from anywhere in the office with Wi-Fi connectivity or use Wi-Fi Direct to print from compatible wireless devices without a Wi-Fi network. You can also print via NFC with a simple tap of a compatible Android device on the printer⁴. Epson's free mobile printing apps and solutions provide further versatility; Email Print allows you to send items to print from almost anywhere in the world⁵.

DATASHEET



KEY FEATURES

- **High-quality A3 printer**
Double-sided A3 printing and dual A3 paper trays
- **Fast business-quality printing**
18ppm in black and 10ppm in colour¹
- **Cost-effective inks**
Up to 50% lower cost-per page than competitive lasers²
- **Wireless solutions**
Ethernet, Wi-Fi, Wi-Fi Direct, NFC⁴ and Scan-to-Cloud⁵
- **Epson's free mobile printing apps**
Freedom to print and scan from almost anywhere⁵



PRODUCT SPECIFICATIONS

TECHNOLOGY

Printing Method	PrecisionCore™ Print Head
Minimum Droplet Size	2.8 pl
Ink Technology	DURABrite™ Ultra
Nozzle Configuration	800 Nozzles black, 256 Nozzles per colour

PRINT

Printing Speed ISO/IEC 24734	18 pages/min Monochrome, 10 pages/min Colour
Maximum Printing Speed	32 pages/min Monochrome (plain paper), 20 pages/min Colour (plain paper)
Printing Resolution	4,800 x 2,400 dpi
Max Duty cycle	20,000 pages per month
Colours	Black, Cyan, Yellow, Magenta

For detailed information on printing speeds please visit <http://www.epson.eu/testing>.

PAPER / MEDIA HANDLING

Paper Formats	A3+, A3, A4, A5, A6, B4, B5, C4 (Envelope), C6 (Envelope), DL (Envelope), No. 10 (Envelope), Letter, 9 x 13 cm, 10 x 15 cm, 13 x 18 cm, 16:9, User defined, Legal
Duplex	Yes (A4/A3, plain paper)
Paper Tray Capacity	500 Sheets Standard, 500 Sheets maximum
Number of paper trays	2

CONNECTIVITY

Interfaces	Hi-Speed USB - compatible with USB 2.0 specification, Ethernet interface (100 Base-TX / 10 Base-T), Wireless LAN IEEE 802.11b/g/n, Wi-Fi Direct
WLAN Security	WEP 64 Bit, WEP 128 Bit, WPA PSK (TKIP), WPA PSK (AES)

GENERAL

Energy Use	1.5 W (sleep mode), 22 W (printing), 5.8 W (Ready), 0.3 W (Power off), ENERGY STAR® qualified
Product dimensions	567 x 424 x 304 mm (Width x Depth x Height)
Product weight	15.5 kg
Compatible Operating Systems	Mac OS 10.5.8 or later, Windows 10, Windows 7, Windows 8, Windows Server 2003 (32/64bit), Windows Server 2008 (32/64bit), Windows Server 2008 R2, Windows Server 2012 (64bit), Windows Vista, Windows XP, Windows server 2003 R2

ADDITIONAL FEATURES

LCD screen	Type: Monochrome, Diagonal: 5.6 cm
------------	------------------------------------

OTHER FEATURES

Emulations	ESC/P-R
------------	---------

OTHER

Warranty	12 months On-site service Optional warranty extension available
----------	--

LOGISTICS INFORMATION

SKU	C11CG38401
EAN code	8715946631097
Dimensions Single Carton	726 x 563 x 416 mm
Carton Weight	18.5 Kg
Country of Origin	Indonesia
Pallet Size Euro	10 Units (2 x 5)
Pallet Size Block	10 Units (2 x 5)



For more information please contact:

Home users: 0343 90 37766
Business users*: 0871 42 37766
Republic of Ireland: 01 436 7742
Or visit us at <https://www.epson.co.uk/contactus>
* 10p per minute plus network extras.

Web: www.epson.co.uk
www.epson.ie

Trademarks and registered trademarks are the property of Seiko Epson Corporation or their respective owners. Product information is subject to change without prior notice.

WorkForce WF-7210DTW

WHAT'S IN THE BOX

- CD Manual
- Driver and utilities (CD)
- Individual Ink Cartridges
- Main unit
- Quick Start Guide
- Software (CD)
- Warranty document
- Power Code

INK YIELD DATA



Alarm clock
27XL

Alarm clock
27XXL



1,100 pages*

2,200 pages*



1,100 pages*

* Approx. page yield based on ISO/IEC 24711/24712 or ISO/IEC 29102/29103. Actual yield will vary depending on images printed and usage conditions. For more information visit <http://www.epson.eu/pageyield>

1. Determined in accordance with ISO/IEC 24734 showing the average of ESAT from the Office Category Test for default A4 simplex. For more information, please visit www.epson.eu/testing
2. For more information visit www.epson.eu/inkjetsaving
3. Approx. page yield based on ISO/IEC 24711/24712. Actual yield will vary depending on images printed and usage conditions. For more information visit www.epson.eu/pageyield
4. Requires NFC and Wi-Fi Direct enabled device with Android OS 4.0 or higher. Requires download of Epson iPrint app from Google Play.
5. Epson iPrint requires a wireless connection and the Epson printing app. Epson Email print, Epson Remote Print Driver and Epson Scan-to-Cloud require an internet connection. For more information, supported languages and devices, please visit www.epsonconnect.eu

EPSON®