



Nokia, 2.4 2/32GB D.Sim - Dusk

## DATA SHEET

### Product Information

Brand	Nokia
SKU	10308384
Manu Part #	719901124301

### Features

Feature 1	Snap after dark with Night mode and get stunning selfies in Portrait mode
Feature 2	Whatever you do, do it bigger on the 6.5" HD+ screen
Feature 3	Get the very latest security and Android features for years to come
Feature 4	A smarter battery means less charging, with up to 2 days of life

### Weight & dimensions

Weight	189 g
Width	76.3 mm
Depth	8.69 mm

Height	165.8 mm
--------	----------

## Design

Product colour	Purple
Form factor	Bar

## Display

Display diagonal	16.5 cm (6.5)
Touchscreen	Y
Screen shape	Flat
Touchscreen type	Capacitive
Rounded display corners	Y

## Network

Bluetooth	Y
Wi-Fi	Y
Wi-Fi standards	802.11b,802.11g,Wi-Fi 4 (802.11n)
Mobile network generation	4G
SIM card type	NanoSIM
SIM card capability	Dual SIM

Tethering (modem-mode)	Y
Bluetooth version	5

## Processor

Processor family	MediaTek
Processor model	Helio P22

## Packaging content

Cables included	Micro-USB
AC adapter included	Y
Quick start guide	Y
SIM card ejector pin	Y

## Software

Operating system installed	Android 10.0
Platform	Android
Virtual assistant	Google Assistant

## Storage

Compatible memory cards	MicroSD (TransFlash)
-------------------------	----------------------

Internal storage capacity	32 GB
Maximum memory card size	512 GB
RAM capacity	2 GB

## Ports & interfaces

USB port	Y
Headphone connectivity	3.5 mm
USB connector type	Micro-USB

## Camera

Front camera resolution (numeric)	5 MP
Rear camera resolution (numeric)	13 MP
Rear camera type	Dual camera
Rear camera flash	Y
Geotagging	Y
Front camera type	Single camera
Second rear camera resolution (numeric)	2 MP
Front camera flash	N

## Battery

Battery capacity	4500 mAh
Wireless charging	N

## Navigation

Position location	Y
GLONASS	Y
GPS (satellite)	Y
BeiDou	Y

## Sensors

Proximity sensor	Y
Ambient light sensor	Y
Accelerometer	Y
Gyroscope	Y

## Subscription

Subscription type	No subscription
-------------------	-----------------

## Messaging

E-mail	Y
--------	---

Short Message Service (SMS)	Y
Multimedia Messaging Service (MMS)	Y

## Performance

Fingerprint reader	Y
Speakerphone	Y

## Multimedia

FM radio	Y
----------	---

---

# Product Description

**NIGHT MODE** Details in the dark Moments worth capturing don't always happen in the light of day. With Night mode's advanced image fusion and exposure stacking, you can capture vibrant detail in darker conditions. **PORTRAIT MODE** Strike a pose Art direct your world with Portrait mode's custom shapes and blurred backgrounds. Plus, with the new Portrait editor, you can refocus and edit pictures long after you've snapped them. **2-DAY BATTERY LIFE** Goes on and on and on... Get up to 2 days out of Nokia 2.4 on a single charge<sup>1</sup>. The 4500 mAh AI-assisted Adaptive Battery prioritizes power for the apps you use most – so you can keep doing what you love. **6.5" HD+ FULL SCREEN** Go big Watch, learn and create on the 6.5" HD+ full display – complete with a selfie notch to maximize your screen experience. **FINGERPRINT SENSOR** Effortless access Unlock your device quickly and easily with a convenient fingerprint sensor, or simply use the AI face unlock – so your phone stays yours. **DESIGN** Strong Finnish roots The 3D Nano-textured cover sits securely in your hand and has a stunning Nordic finish. Plus, the diecast metal chassis and polycarbonate shell give your phone a comfortable, solid feel. **ANDROID ONE** Ready for what's next Enjoy the pure software experience of a streamlined interface and no bloatware. Plus, stay on top of the latest Android™ features with 3 years of monthly security updates and 2 years of software upgrades. **GOOGLE ASSISTANT BUTTON** A little help wherever you go Google Assistant on mobile is always with you – so you can get things done fast with just your voice. Manage tasks, create lists and get directions on the go after one press of the button.

