

## PRECISION Series










# Roebuck

Specifically designed for precision work. Thermoplastic rubber handle in the area of rotation. Rotating head allows the tip to be perfectly positioned for fast and comfortable finger movement during use. High accuracy shanks manufactured from molybdenum vanadium alloy steel, chrome plated with black tip.

### 6 piece set available containing:

Slotted	50 x 1.5	Pozidriv	50 x 3.0
	50 x 2.0		No. 0
	50 x 2.5		No. 1

233087

	Blade Length	Tip Size	Order Code	Price Each
	<b>Slotted</b>			
	50	1.2 mm	<b>385-8492</b>	
	50	1 mm	<b>385-8509</b>	
	50	1.5 mm	<b>385-8510</b>	
	50	2 mm	<b>385-8522</b>	
	75	2 mm	<b>385-8534</b>	
	50	2.5 mm	<b>385-8546</b>	
	100	2.5 mm	<b>385-8558</b>	
	50	3 mm	<b>385-8560</b>	
	100	3 mm	<b>385-8571</b>	
	200	3 mm	<b>385-8583</b>	
	75	3.5 mm	<b>385-8595</b>	
	75	4 mm	<b>385-8601</b>	
	250	4 mm	<b>385-8613</b>	
	<b>Phillips</b>			
	50	No.0	<b>385-8625</b>	
	50	No.0	<b>385-8637</b>	
	200	No.0	<b>385-8649</b>	
	75	No.1	<b>385-8650</b>	
	250	No.1	<b>385-8662</b>	
	<b>Pozidriv</b>			
	50	No.0	<b>385-8674</b>	
	75	No.1	<b>385-8686</b>	
	<b>Torx</b>			
	50	T6	<b>385-8698</b>	
	50	T7	<b>385-8704</b>	
	50	T8	<b>385-8716</b>	
	50	T9	<b>385-8728</b>	
	50	T10	<b>385-8730</b>	
	75	T15	<b>385-8741</b>	
	75	T20	<b>385-8753</b>	
	<b>Allen Tip</b>			
	50	Hex 0.9	<b>385-8765</b>	
	50	Hex 1.3	<b>385-8777</b>	
	50		<b>385-8789</b>	
	50	Hex 2.0	<b>385-8790</b>	
	50	Hex 2.5	<b>385-8807</b>	
	50	Hex 3.0	<b>385-8819</b>	
	<b>Hexagonal Ball Tip</b>			
	50	Hex 1.5	<b>385-8820</b>	
	50	Hex 2.0	<b>385-8832</b>	
	50	Hex 2.5	<b>385-8844</b>	
	75	Hex 3.0	<b>385-8856</b>	
	<b>Set</b>			
	6 piece		<b>385-8868</b>	