


31

2,5 MS

Minimodul™ connectors, pitch 2.5 mm




Minimodul™ pin header

State: Phasing out

31

2,5 MS



Environmental conditions

Temperature range -40 °C/+110 °C

Materials

Insulating body PA GF, V-0 according to UL94
Contact pin CuZn, pre-nickel and tin-plated

Electrical data (at T_{amb} 20 °C)

Rated current 5 A
Rated voltage 250 V AC
Rated impulse voltage 2 kV/60 s
Creepage distance 1,9 mm
Clearance 1,9 mm
Insulation resistance > 1 GΩ

Associated products

Counterparts
 ↗ 2,5 MB ↗ 2,5 MBPH ↗ 2,54 MKB
 ↗ 2,54 MKBL ↗ 3114 ↗ 4143 01

Designation	Pole Number	PU (Pieces)	MDQ (Pieces)
2,5 MS 02	2	250	5000
2,5 MS 03	3	250	5000
2,5 MS 04	4	250	5000
2,5 MS 05	5	250	5000
2,5 MS 06	6	250	5000
2,5 MS 07	7	250	5000
2,5 MS 08	8	250	5000
2,5 MS 09	9	250	5000
2,5 MS 10	10	250	5000
2,5 MS 11	11	250	5000
2,5 MS 12	12	250	5000
2,5 MS 13	13	250	5000
2,5 MS 14	14	250	5000
2,5 MS 15	15	250	5000
2,5 MS 16	16	250	5000
2,5 MS 17	17	250	5000
2,5 MS 18	18	250	5000
2,5 MS 19	19	250	5000
2,5 MS 20	20	200	5000

Packaging:

in bulk, in a cardboard box