

Banner's Call for Parts creates a steady workflow and pinpoints critical issues. [Learn more.](#)

# ABR72L16-RDE2

## ▶ ABR BARCODE SERIES




ABR Series Barcode Reader

Resolution: 1600x1200 px; Lens: 16 mm Autofocus;  
Light: Red; Diffused


Ethernet & Serial Communications; 1D + 2D  
Code

Part Number: 808841



## SPECIFICATIONS

<b>IP Rating</b>	IP67
<b>Autofocus</b>	Yes
<b>Device Type</b>	Imager BCR
<b>Primary Housing Material</b>	Aluminum
<b>Camera Housing Size (HxWxL mm)</b>	43 x 54 x 95
<b>Image Resolution</b>	1600 x 1200 pixels
<b>Lens (mm)</b>	16
<b>Light Color</b>	Red
<b>Code Type</b>	1D, 2D
<b>Imager Type</b>	Grayscale

 Offline (Contact Us)

<b>Feature: PC Interface</b>	Yes
<b>EtherNet/IP</b>	Yes
<b>Common Ethernet Protocol</b>	No
<b>Modbus/TCP</b>	Yes
<b>PCCC</b>	No
<b>PROFINET</b>	No
<b>RS-232</b>	Yes
<b>RS-422</b>	Yes
<b>FTP</b>	Yes
<b>USB</b>	No

## COMPATIBLE PRODUCTS

### BRACKET

	<p><b>SMBABR7RA</b></p> <p>Replacement Bracket for ABR 7000 Series Right-Angle Bracket Zinc-Coated Steel</p>
--	--

### DOUBLE-ENDED CORDSETS

	<p><b>MQDEC-1703SS-DB25</b></p> <p>Euro-Style to DB25 Shielded Cable 17 Pin Female Straight to DB25 Male 0.91 m (3 ft) Length Black, PVC, Nickel Plated Coupling Nut</p>
	<p><b>MQDEC-1706SS</b></p> <p>Euro-Style Double Ended Shielded Cable 17 Pin Female Straight to 17 Pin Male Straight 1.83 m (6 ft) Length Black, PVC, Nickel Plated Coupling Nut</p>

	<p><b>MQDEC-1715SS</b></p> <p>Euro-Style Double Ended Shielded Cable  17 Pin Female Straight to 17 Pin Male Straight  4.57 m (15 ft) Length  Black, PVC, Nickel Plated Coupling Nut</p>
	<p><b>MQDEC-1730SS</b></p> <p>Euro-Style Double Ended Shielded Cable  17 Pin Female Straight to 17 Pin Male Straight  9.14 m (30 ft) Length  Black, PVC, Nickel Plated Coupling Nut</p>
	<p><b>STP-M12D-406</b></p> <p>Euro-Style M12 D-Code to RJ45 Ethernet Cable  4 Pin Male Straight to RJ45  1.83 m (6 ft) Length  Teal, PVC, Nickel Plated Coupling Nut</p>
	<p><b>STP-M12D-415</b></p> <p>Euro-Style M12 D-Code to RJ45 Ethernet Cable  4 Pin Male Straight to RJ45  4.57 m (15 ft) Length  Teal, PVC, Nickel Plated Coupling Nut</p>
	<p><b>STP-M12D-430</b></p> <p>Euro-Style M12 D-Code to RJ45 Ethernet Cable  4 Pin Male Straight to RJ45  9.14 m (30 ft) Length  Teal, PVC, Nickel Plated Coupling Nut</p>

## SINGLE-ENDED CORDSETS

	<p><b>MQDC2S-1706</b></p> <p>Euro-Style Quick Disconnect Shielded Cable  17 Pin Straight Connector  1.83 m (6 ft) Length  Black, PVC, Nickel Plated Coupling Nut</p>
	<p><b>MQDC2S-1715</b></p> <p>Euro-Style Quick Disconnect Shielded Cable  17 Pin Straight Connector  4.57 m (15 ft) Length  Black, PVC, Nickel Plated Coupling Nut</p>

**MQDC2S-1730**

Euro-Style Quick Disconnect Shielded Cable  
17 Pin Straight Connector  
9.14 m (30 ft) Length  
Black, PVC, Nickel Plated Coupling Nut

**MISCELLANEOUS****TCNM-ACBB1**

Barcode reader connection box for simplified wiring and integration  
For use with ABR and TCNM barcode products

**TCNM-ACMK-100**

Barcode Memory Module; Provides backup and restore capability; Used with TCNM-ACBB1 connection box and ABR barcode reader



Banner Engineering Corp. | 9714 Tenth Avenue North | Minneapolis, MN 55441 | United States of America