



## EX-40/8

Order No.: 0163410

### PRODUCTINFOS

#### Audio exciters/resonators, 20 W, 4 Ω (/4) or 8 Ω (/8)

Exciters are suitable for music and voice reproductions via surfaces capable of vibrating. They are simply glued onto doors, cupboard doors, shelves, desktops, lightweight walls, ceiling panels or many other surfaces which are capable of vibrating. Vibration of these surfaces create an impressive sound in the entire surrounding area.

- Depending on the mounting surface, very wide bandwidth reproduction with amazing volumes
- Excellent sound quality
- High power capability
- Suitable for unobtrusive PA applications, e.g. at doors, cupboards, shelves, glass panels
- Supplied with 3M adhesive pad

### TECHNICAL SPECIFICATIONS

#### EX-40/8

Impedance (Z)

8 Ω

Frequency range

fx-20,000 Hz

**EX-40/8**

Resonant frequency (fs)	300 Hz
Power rating (RMS)	20 W
Peak music power output (MAX)	40 W
Max. rated SPL	no data
Voice coil diameter	Ø 32 mm
Voice coil former	KSV
Dimensions	Ø 61 mm x 20 mm
Outside diameter	Ø 61 mm
Width	61 mm
Height	61 mm
Depth	20 mm
Admiss. ambient temp.	0-40 °C
Weight	0.129 kg
Packing unit	1
Packing dimensions (W x H x L)	0.08 x 0.033 x 0.08 m
Gross weight	0.144 kg
Net weight	0.129 kg