

**New****440.JP9 - 440.JP12****9 or 12 piece combination wrench clip set**

440.JP9



440.JP12

**YOUR WRENCHES WITH YOU AT ALL TIMES****Practical : save time**

- Easy, clear wrench identification.
- Quick, foolproof tool storage.
- No more loose wrenches in your tool box.
- Belt hook.
- Hole for wall hook.

**Safe : no more lost wrenches.**

- Missing wrenches readily identified : no more tools left on site at the end of the job.
- Durable wrench locking system.

**Ultra compact**

Total overall dimensions :  
219x66x38 mm for 440.JP9.  
280x87x47 for 440.JP12.

**Easy to store.**

- In any storage compartments of any Facom tool box (BT11, BT13, Probox, etc.).
- In any roller cabinet drawer.



# Combination wrenches

## 440 Clip set of OGV® combination wrenches

- Quickly stored, quickly identified, always with you.
- Chemical product-resistant.


🔧	mm	ΔΔ g
<b>440.JP9</b>	8 - 10 - 11 - 12 - 13 - 16 - 17 - 18 - 19	940
<b>440.JP12</b>	7 - 8 - 10 - 11 - 12 - 13 - 16 - 17 - 18 - 19 - 22 - 24	1548



## 440 Metric OGV® combination wrench sets


- Supplied as box, roll or panel sets.

🔧	📦	📜	📄	mm	ΔΔ g
<b>440.JN8</b>		•		8 - 10 - 11 - 13 - 17 - 19 - 22 - 24	1003
<b>440.JN8T</b>	N.38A-8C			8 - 10 - 11 - 13 - 17 - 19 - 22 - 24	1133
<b>440.JE9</b>		•		8 - 9 - 10 - 11 - 12 - 13 - 14 - 17 - 19	657
<b>440.JE11</b>		•		7 - 8 - 10 - 11 - 12 - 13 - 14 - 16 - 17 - 18 - 19	903
<b>440.JE16</b>		•		8 - 9 - 10 - 11 - 12 - 13 - 14 - 15 - 16 - 17 - 18 - 19 - 21 - 22 - 23 - 24	1989
<b>440.JE16T</b>	N.38A-17A			8 - 9 - 10 - 11 - 12 - 13 - 14 - 15 - 16 - 17 - 18 - 19 - 21 - 22 - 23 - 24	2164
<b>440.JE18</b>		•		6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 - 14 - 15 - 16 - 17 - 18 - 19 - 21 - 22 - 23 - 24	1989
<b>440.JE25</b>				6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 - 14 - 15 - 16 - 17 - 18 - 19 - 21 - 22 - 23 - 24 - 26 - 27 - 28 - 29 - 30 - 32 - 34	5545
<b>440.P25M</b>		•		6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 - 14 - 15 - 16 - 17 - 18 - 19 - 21 - 22 - 23 - 24 - 26 - 27 - 28 - 29 - 30 - 32 - 34	5545



## 440 Inch OGV® combination wrench sets

🔧	📦	📜	mm/"	ΔΔ g
<b>440.JU6T</b>	N.38A-6B		3/8 - 7/16 - 1/2 - 9/16 - 5/8 - 11/16	603
<b>440.JU9</b>		•	1/4 - 5/16 - 3/8 - 7/16 - 1/2 - 9/16 - 5/8 - 11/16 - 3/4	696
<b>440.JU12</b>		•	1/4 - 5/16 - 3/8 - 7/16 - 1/2 - 9/16 - 5/8 - 11/16 - 3/4 - 13/16 - 7/8 - 15/16	1399
<b>440.JU17T</b>	N.38A-17		1/4 - 5/16 - 11/32 - 3/8 - 7/16 - 1/2 - 9/16 - 5/8 - 11/16 - 3/4 - 13/16 - 7/8 - 15/16 - 1" - 11/16" - 11/8" - 11/4"	3350



## 440 OGV® combination wrench sets in thermo-formed modules

- Compatible with the FACOM modular storage system (all roller cabinets).
- MOD.440-1XL and MOD.440-2XL : to fit XL roller cabinets.
- MOD.440-1, MOD.440-2 and MOD.440-4 : to fit all roller cabinets.

🔧	📦	mm/"	ΔΔ g
<b>MOD.440-1XL</b>	PL.313	6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 - 14 - 15 - 16 - 17 - 18 - 19 - 21 - 22 - 24	1938
<b>MOD.440-1</b>	PL.670	6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 - 14 - 15 - 16 - 17 - 18 - 19 - 22 - 24	1733
<b>MOD.440-2XL</b>	PL.671	27 - 29 - 30 - 32 - 34	2920
<b>MOD.440-2</b>	PL.314A	27 - 29 - 30 - 32	1733
<b>MOD.440-4</b>	PL.673	1/4 - 5/16 - 11/32 - 3/8 - 7/16 - 1/2 - 9/16 - 5/8 - 11/16 - 3/4 - 13/16 - 7/8 - 15/16	1593



## 440 OGV® combination wrench sets in foam modules

- Compatible with the FACOM modular storage system (XL roller cabinets).

🔧	📦	mm/"	ΔΔ g
<b>MODM.440-1</b>	PM.MOD440-1	6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 - 14 - 15 - 16 - 17 - 18 - 19 - 21 - 22 - 24	1868
<b>MODM.440-2</b>	PM.MOD440-2	27 - 29 - 30 - 32 - 34	2855

