

2P Male Panel Mount Speaker Connector




Features

- Current rating 40Arms continuous
- Up to 50 A audio signal, duty cycle 50%
- 3 parts, easy to assemble
- High impact materials - long-lasting and reliable
- Solder type wire termination for easy assembly
- 2 Pole Locking Socket PA6 - Polyamide 6GF - Glass Fibre

Specifications

Contact Resistance : 20mΩ
 Dielectric Strength : 1500V AC
 Housing : PA6+15%GF
 Contact Element : Nickel-plated brass

Diagram



No	Description	Material	Finish	Qty
1	Plastic Base	PA	Black	1
2	Terminal -1	Phosphor Bronze	Gold	
3	Back Cover	PA	Black	
4	Terminal -1	Phosphor Bronze	Gold	

Part Number Table

Description	Part Number
2P Male Panel Mount Speaker Connector	27-10159

Dimensions : Millimetres

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
 Farnell.com/multicomp-pro
 Element14.com/multicomp-pro