

# Cables for Golden Dragon, OSLOON & Stanley 6 Strips

## CAB-ILS-GD06-INPUT CAB-ILS-GD06-LINK

### Product Overview

Connection cables for use with to ILS' Golden Dragon, Osolon and Stanley PowerLinear Strips

Employs JST PH type connector

Cable length 300 mm


CAB-ILS-GD06-INPUT: Power Input

CAB-ILS-GD06-LINK: Linking strips

### Ratings etc:


Maximum current	2 amps
Temperature range	-25° to +85° C
Insulation resistance	1,000 m Ohms min
Withstanding voltage	800V AC/minute
RoHS compliant	Yes

\*This datasheet should be read in conjunction with the relevant JST data on the connector used




### Drawings:

CAB-ILS-GD06-INPUT



CAB-ILS-GD06-LINK



### Important Information and Precautions

- Do not exceed the maximum current and voltage
- Minimum bend radius for cables is 5 mm
- Do not pull on cables or use them for physical support

### For further information please contact ILS.

The values contained in this data sheet can change due to technical innovations. Any such changes will be made without separate notification.