

SPECIAL TOOLS



No.	Description	Length	Weight
2-265	Test prods , extremely slim, pointed and flexible, blade made from 1 mm steel wire, with banana plug connection, fully insulated, available in red (2-265-1) and black (2-265-2)	155 mm	9 g
2-125	Desoldering lever for lifting fixed components when desoldering, ends at different angles (40°/70°), slotted at both ends, nickel-plated, insulated	125 mm	7 g
2-126	Desoldering lever , slotted at one end, nickel-plated, round, insulated shank and hexagonal plastic handle	115 mm	10 g
2-127	Tin knife with pointed, sharp blade, for cutting circuit paths and working printed circuit boards, round, insulated shank and hexagonal plastic handle	115 mm	14 g
2-128	Tin scraper with blade of sharp parting tool shape for scraping off excess solder and solder bridges, round, insulated shank and hexagonal plastic handle	115 mm	14 g
2-101	Tin knife with ceramic blade for working printed circuit boards, handle from conductive black plastic	105 mm	9 g
2-135	Core remover for easy removal of damaged cores in coils etc., flexible metal tip 1.5 x 0.5 x 30 mm, nickel-plated blade, BERNSTEINIT handle	175 mm	8 g
2-145	Screwdriver with guide sleeve for easy and accurate setting of spindle resistors and potentiometers with slotted axles up to 3.2 mm Ø, nickel-plated blade, plastic-handle	140 mm	12 g
2-151	Triangular scraper in brass tool holder, nickel-plated, triangular blade made from hollow ground special steel (80 mm long), insertable at both ends and adjustable in holder	90 mm	26 g
2-152	Tool holder , nickel-plated brass, with collets at both ends for holding tools from 0 to 3 mm Ø	110 mm	32 g
2-155	Claw-type gripper , nickel-plated brass, with 4 wire claws, small version with clip	120 mm	21 g
2-157	Flexible claw-type grip with 4 sprung claws, to reach inaccessible areas with free play, nickel-plated, long version	600 mm	75 g
2-161	Magnetic bar with double ball-and-socket joint, slewable into any position, diameter of bar 8 mm	215 mm	34 g
2-165	Contact cleaner , brush-type, with wire bristles, nickel-plated	35 mm	2 g
2-166	Glass fibre contact cleaner brush with rotary mechanism, plastic casing	115 mm	10 g
2-167	Replacement glass fibre for 2-166	40 mm	1 g
2-234	High voltage tester made from BERNSTEINIT with steel tip	190 mm	15 g
2-236	Valve tapping hammer made from BERNSTEINIT	170 mm	15 g
2-245	Resilient adjusting key for bending and adjusting fine contacts, nickel-plated blade, BERNSTEINIT handle	135 mm	11 g