

ERSA Multitip-Series

Multitip 8 W

132 BD / 132 BN

132 LD / 132 LN

132 KD / 132 KN

Multitip 15 W

162 BD / 162 BN

162 LD / 162 LN

162 KD / 162 KN

Multitip 25 W

172 BD / 172 BN

172 LD / 172 LN

172 KD / 172 KN

Dimensions in brackets for ERSADUR long-life soldering tips (for tip design see page 14)



Electronics Entry Set (15 W)
910 BD 0035

Multitip Workbox (25 W)
920 LD 0035

ERSA Multitip 8 W

A particularly short, light and easy-to-handle soldering iron with a minimum distance between the soldering tip and the front part of the handle. Ideal for ultra-fine soldering requirements. Internally heated soldering tips ensure major performance.

Technical data:

Rating: 8 W
Heating time: appr. 90 s
Sold. tip temperature: appr. 290°C/554°F
Weight (without cable): 26 g / 0.92 oz
Cable: 1.5 m / 4.9 ft PVC
Voltage: 230 V
Different voltages on request

Order nos.:

900 BN ERSA Multitip 08 soldering iron with 132 BN nickel-plated copper soldering tip and A 18 tool holder
900 BD ERSA Multitip 08 soldering iron with 132 BD long-life soldering tip and tool holder A 18
90100 Spare heating element for Multitip 08

ERSA Multitip 15 W

This type is particularly suitable to solder small relay connections. Internally heated soldering tips ensure major performance. PTC (Positive Temperature Coefficient) heating element for short heating times and a remarkably long service life.

Technical data:

Rating: 15 W
Heating time: appr. 60 s
Sold. tip temperature: appr. 350°C/662°F
Weight (without cable): 28 g / 1 oz
Cable: 1.5 m / 4.9 ft PVC
Voltage: 230 V
Different voltages on request

Order nos.:

910 BN ERSA Multitip C15 soldering iron with 162 BN nickel-plated copper soldering tip and A 18 tool holder
910 BD ERSA Multitip C15 sold. iron with 162 BD long-life sold. tip and A 18 tool holder
91100 Spare heating element for Multitip C 15
910 BD 0035 Electronics entry set with Multitip 15 sold. iron, 162 BD /162 KD ERSADUR long life sold. tips, A19 tool holder, antistatic solder sucker, desoldering wick, solder guide and 7 g (0.3 oz) solder

ERSA Multitip 25 W

Due to a rating of 25 W, this is the ideal sold. iron for medium-size soldering requirements such as distribution strips and hobby soldering. The internal heating ensures major performance. PTC heating element for short heating times and a remarkably long service life.

Technical data:

Rating: 25 W
Heating time: appr. 60 s
Sold. tip temperature: appr. 450°C/842°F
Weight (without cable): 34 g / 1.2 oz
Cable: 1.5 m / 4.9 ft PVC
Voltage: 230 V
Different voltages on request

Order nos.:

920 BN ERSA Multitip C25 sold. iron with 172 BN nickel-plated copper soldering tip and A 18 tool holder
920 BD ERSA Multitip C25 sold. iron with 172 BD long-life sold. tip and A 18 tool holder
92100 Spare heating element for Multitip C 25
920 LD 0035 Multitip Workbox, complete, containing Multitip C25 sold. iron, 172 LD / 172 BD long-life sold. tips, A 18 tool holder, VAC 3 solder sucker and 7 g (0.25 oz) solder (see top fig.)