


Tiefenmeßschieber mit gerader Meßstange

Ausführung:

DIN 862
rostfreier Stahl
Ablese­teile mattverchromt
Fest­stellschraube
einschließlich Etui



120-01

Vernier depth gauges without hook



Techn. data:

DIN 862
stainless steel
satin chromed reading parts
locking screw
individually packed

Jauges de profondeur sans talon

Applications:


DIN 862
en inox
lecture chromée mate
vis de blocage
emballées à l'unité

> mm <	 mm	 mm	No.	€	Calibr ...K
150	0,05	100	120-00	23,80	6,80
200	0,05	100	120-01	26,40	13,00
300	0,05	125	120-02	29,90	15,80

Tiefenmeßschieber mit Hakenmeßstange

Ausführung:

DIN 862
rostfreier Stahl
Ablese­teile mattverchromt
Fest­stellschraube
einschließlich Etui



120-10

Vernier depth gauges with hook



Techn. data:

DIN 862
stainless steel
satin chromed reading parts
locking screw
individually packed

Jauges de profondeur avec talon

Applications:

DIN 862
en inox
lecture chromée mate
vis de blocage
emballés à l'unité

> mm <	 mm	 mm	No.	€	Calibr ...K
150	0,05	100	120-09	32,15	6,80
200	0,05	100	120-10	36,30	13,00
300	0,05	125	120-11	42,00	15,80

> mm <



Messbereich

Ablesung mm / inch



Brückenlänge

Range

Reading mm / inch

Length of base

Capacité

Lecture mm / inch

Longueur de base